

## Type Approval Certificate

This is to certify that the undernoted product(s) has/have been tested with satisfactory results in accordance with the relevant requirements of the Lloyd's Register Type Approval System.

<b>Manufacturer</b>	<b>Danfoss Drives A/C</b>
<b>Address</b>	DK-6300, Graasten, Denmark
<b>Place of Production</b>	AuCom Electronics Limited 123 Wrights Road, Addington, Christchurch, 8440, New Zealand
<b>Type</b>	Soft Starters
<b>Description</b>	MCD200 series soft starters for electric motors MCD 20w-xxx-Ty-CVz Where:- W=Designates the features of the starter 1=without motor protection 2=with motor protection (overload, phase loss, excess start time, etc.) xxx=designates the nominal motor rating; 007 kW to 110kW Y=designates the maximum voltage rating; 6=575V a.c. Z=designates the control supply voltage 3=110 to 240V a.c. & 380 to 440V a.c. 1=24V a.c. or d.c.
<b>Trade Name</b>	MCD200
<b>Application</b>	Soft starter for three phase electric motors for Marine, offshore and industrial applications for use in environmental categories ENV2 in the "Bridge and Deck Zone" as defined in LR Type Approval System Test Specification No. 1 1-2002 where the Test Specification is satisfactory for the intended operation.

19th Floor, 550 Yan An dong Road, Shanghai,  
Huangpu District, China

---

**Ke Lin Zhang**

Senior Specialist to Lloyd's Register  
Classification Society (China) Co Ltd  
A member of the Lloyd's Register group

Lloyd's Register Group Limited, its affiliates and subsidiaries and their respective officers, employees or agents are, individually and collectively, referred to in this clause as 'Lloyd's Register'. Lloyd's Register assumes no responsibility and shall not be liable to any person for any loss, damage or expense caused by reliance on the information or advice in this document or howsoever provided, unless that person has signed a contract with the relevant Lloyd's Register entity for the provision of this information or advice and in that case any responsibility or liability is exclusively on the terms and conditions set out in that contract.

## Type Approval Certificate

**Specified Standard** Identical with CSX soft starters for electric motors in LR type approval certificate No. 04/10097(E2) issued to AuCom Electronics Limited.  
Correspondence between CSX series and MCD200 series: "Description of product" 720 04051-00A MCD200 Lloyd's Description.doc.

Ratings	Type	Motor kW	Operational current(A)
	007	007	18
	015	015	34
	018	018	42
	022	022	48
	030	030	60
	037	037	75
	045	045	85
	055	055	100
	075	075	140
	090	090	170
	0110	110	200

Operational voltage (V): T6=200-575

Remarks: control supply: Freq.=45-66 Hz;

Volt.: CV3=11-240 V a.c.

380-440 V a.c.

CV1=24 V a.c./d.c.

**Additional Tests** Low Temperature Test at -10°  
Dry heat test at 60°C

**Other Conditions**

1. The certificate attests to the hardware's suitability for the environmental categories stated.
2. Suitability of the software and system configurations is subject to a separate plan appraisal according to Lloyd's Register Rules and Regulations when placed on Lloyd's Register classed vessels.

This certificate is not valid for equipment, the design, ratings or operating parameters of which have been varied from the specimen tested. The manufacturer should notify Lloyd's Register Classification Society (China) Co Ltd of any modification or changes to the equipment in order to obtain a valid Certificate.

The Design Appraisal Document No. LR2037188TA and its supplementary Type Approval Terms and Conditions form part of this Certificate.

19th Floor, 550 Yan An dong Road, Shanghai,  
Huangpu District, China

Lloyd's Register Group Limited, its affiliates and subsidiaries and their respective officers, employees or agents are, individually and collectively, referred to in this clause as 'Lloyd's Register'. Lloyd's Register assumes no responsibility and shall not be liable to any person for any loss, damage or expense caused by reliance on the information or advice in this document or howsoever provided, unless that person has signed a contract with the relevant Lloyd's Register entity for the provision of this information or advice and in that case any responsibility or liability is exclusively on the terms and conditions set out in that contract.