

Product Readymade Self-limiting heating cable

Applicant Danfoss A/S  
Nordborgvej 81  
DK 6430 Nordborg  
Denmark

Manufacturer Danfoss A/S  
Nordborgvej 81  
DK 6430 Nordborg  
Denmark

Factory Danfoss Poland Sp. z.o.o  
Ul. Chrzanowska 5  
05-825 Grodzisk Mazowiecki  
Poland

Ratings 10W/m (at 10°C) 230V~

Trade mark



Model / Type Ref. ECpipeheat 10 V3

Principal characteristics Cl. I. IP67. The appliances can be delivered in lengths from 2m to maximum 25m.

A sample of the product was tested and found to be in conformity with HOUS EN 60335-1:2012;A11;A13;A1;A14;A2  
EMF EN 62233:2008

Validity This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation.  
New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.

Additional information

Additional model(s) (1) See page 2

Date of issue 13-07-2021



Juan Z. Saussey  
Certification Department

**Nemko AS**

Philip Pedersens vei 11, 1366 Lysaker, Norway  
TEL +47 22 96 03 30 EMAIL [info@nemko.com](mailto:info@nemko.com)  
ENTERPRISE NUMBER NO974404532

[nemko.com](http://nemko.com)

# CERTIFICATE

No. P21225608



Additional model(s)

Product

Readymade Self-limiting heating cable

1

DEVIpipeheat™ 10 V3



Rating

10W/m (at 10°C) 230V~

Principal characteristics

Cl. I. IP67. The appliances can be delivered in lengths from 2m to maximum 25m.

Date of issue 13-07-2021



Juan Z. Saussey

Certification Department

**Nemko AS**

Philip Pedersens vei 11, 1366 Lysaker, Norway

TEL +47 22 96 03 30 EMAIL [info@nemko.com](mailto:info@nemko.com)

ENTERPRISE NUMBER NO974404532