



产品认证证书

证书编号: CQC20002261984

发证日期: 2023 年 11 月 13 日
有效期至: 2028 年 11 月 12 日

委托人名称 Danfoss A/S
及注册地址 Nordborgvej 81, 6430 Nordborg, Denmark

制造商名称 Danfoss A/S
及注册地址 Nordborgvej 81, 6430 Nordborg, Denmark

生产企业名称 Wendell Electronics a.s.
及生产地址 Nádražní 1179, Lanskroun, 563 01, Czech Republic

产品名称和系列、规格、型号 温控器
EETa 系列 100-240Vac±10% 16A 50Hz/60Hz 1B 型 -25T55 动作温度范围: -10°C-55°C 插片
端子 污染等级 2 PTI175

产品标准和技术要求 GB/T 14536.1-2022;GB/T 14536.10-2022

认证模式 型式试验+获证后监督

上述产品符合 CQC11-448321-2016 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020 年 08 月 20 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0568125



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC20002261984

Valid from: Nov.13,2023

Valid until:Nov.12,2028

NAME AND REGISTERED ADDRESS OF THE APPLICANT Danfoss A/S
Nordborgvej 81, 6430 Nordborg, Denmark

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Danfoss A/S
Nordborgvej 81, 6430 Nordborg, Denmark

NAME AND LOCATION OF THE FACTORY Wendell Electronics a.s.
Nádražní 1179, Lanskrout, 563 01, Czech Republic

PRODUCT NAME, MODEL AND SPECIFICATION Electronic Thermostat Controller
EETa series, 100-240Vac±10% 16A 50Hz/60Hz 1B 型 -25T55 Operating temperature range:
-10°C-55°C Plug terminal Pollution degree 2 PTI175

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14536.1-2022;GB/T 14536.10-2022

TYPE OF CERTIFICATION SCHEMES type test+follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-448321-2016.

Date of original issued: Aug.20,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C 0568125