

# Certificate

## Quality Assurance System acc. to Directive 2014/68/EU

Certificate no.: 01 202 931/Q-04 0018.00

Name and address of the  
certificate holder:  
**Danfoss Saginomiya Sp. z o.o.**  
**Chrzanowska 5**  
**05-825 Grodzisk Mazowiecki**  
**Poland**

Herewith we certify that the above -mentioned manufacturer  
operates a quality system according to the European Directive  
2014/68/EU.

The manufacturer has the permission to affix the following  
CE marking to pressure equipment described and  
manufactured in accordance to the scope covered by this  
Quality-Assurance System:

**CE 0035**

Test basis: **Directive 2014/68/EU: QA-System (Module D)**  
(the QS-Modules E1, E, D1 are covered by Module D)

Audit report no.: 01 202 931/Q-04 0018

Scope: **Pressure limiting devices for refrigeration, air conditioning  
systems and heat pumps, see annex to certificate:  
01 202 931/Q-04 0018, revision 6 from 03.12.2024**

Manufacturing plant: see certificate holder

Validity: **This certificate is valid until 2028-01-22.**

Cologne, 2025-01-21

Ines Krüger-Führ



Details of the Validity of the Approval as Manufacturer of Pressure Equipment  
with certified QA-System acc. PED 2014/68/EU



Annex to Certificate No.: 01 202 931/Q-04 0018

Manufacturer		Manufacturing Plant		Nationality	Date	Page No.	TÜV Rheinland Industrie Service GmbH
Company Name: Danfoss Saginomiya Sp. z o.o. Location: Ul. Chrzanowska 5, 05-825 Grodzisk Mazowiecki		Danfoss Saginomiya Sp. z o.o. Ul. Chrzanowska 5 05-825 Grodzisk Mazowiecki		PL	03.12.2024	1	
					Rev.: 6	of: 1	
Item No.	Product description	Until now applied codes	Material	Limitations / Restrictions	List of Module B (E)/ B (B) Certificates (by QS-Module D/E)	Remark	
1	2	3	4	5	6	7	
01	Pressure Limiting Device: <b>ACB-1T...(W), ACB-2T...(W), ACB-4T...(W)</b> <b>ACB-1U...(W), ACB-2U...(W), ACB-4U...(W)</b> <b>ACB-1U...(MW), ACB-2U...(MW), ACB-4U...(MW)</b>	DIN EN 12263:1999	Stainless Steel	Max. PS: 50 bar Max. TS: -30°C...+85°C Pressure Limit (adjust.): 20...50 bar	01 202 641/B-19-0020-03		
02	<b>ACB-series</b> <b>LCB-series</b>	DIN EN 12263:1999	Stainless Steel	Max. PS: 45 bar For protection of airconditioning and refrigerating systems in category II.	-		Category II ( module D1)
03	Pressure Limiting Device: <b>CKB-(1, 2, 3, 4)UC(S, K, L)(A, M, N)</b>	DIN EN 12263:1999	Stainless Steel	Max. PS: 143 bar Max. TS: -40°C...+70°C	01 202 641/B-19-0023-02		