

Product Overview

Radiator thermostats and valves

ENGINEERING
TOMORROW



Mechanical Radiator Thermostats

Electronic Radiator Thermostats



		Basic RAS-C2	Design RAX	Pro RAW	Premium RA2000	Danfoss Eco™ In-home control	Danfoss Ally™ Control from anywhere*
Features	Energy saving						
	Comfort level						
	Reaction time						
	Installation	 Parrot nose pliers	 Allen key	 Easy Click-lock	 Easy Click-lock	 Easy adapter solution	 Easy adapter solution
	Valve connection	RA	RA, M30	RA, M30	RA, RAV, RAVL, RTD	RA, RAV, RAVL, RTD, M28, M30	RA, RAV, RAVL, RTD, M28, M30

*Danfoss Ally™ Gateway required

Radiator Valves



		Fixed Capacity RA-FN	Pre-setting RA-N	Pressure Independent RA-Dynamic
Features	Energy saving			
	Hydronic balancing			
	Noise level			
	Easy pre-setting		 Easy	 Easiest
	Easy pump optimization		 Easy	 Easiest

Did you know that you can get up to **10 years warranty** with Danfoss?
 ➤ Go to trv.danfoss.com for more information