

# Instructions

# ESM-11

ENGINEERING  
TOMORROW



**1**

**2**

**3**

**4**

**5**

**6**

**7**

**8**

**9**

0,3 - 1,5 mm<sup>2</sup>

Ø 3 - 7 mm

**MIN:**  
Ø 21 mm  
DN15

**MAX:**  
Ø 76 mm  
DN65

Temperature (°C)	Resistance (Ω)
0	1000
20	1050
40	1100
60	1150
80	1200
100	1250
120	1300
120	1450

DHS-SMDT/DK

AN00008644509900-000301 © Danfoss 12/2020

1