

Product Overview

Radiator thermostats and valves

ENGINEERING
TOMORROW



Mechanical Radiator Thermostats

Electronic Radiator Thermostats



		Standard RAS-C2	Design RAS-D2	Premium RA2000	Danfoss Eco™ In-home control
Features	Energy saving				
	Comfort level				
	Reaction time				
	Installation	 Parrot nose pliers	 Allen key	 Easy Click-lock	 Easy adapter solution
	Valve connection	RA	RA	RA, RAV, RAVL, RTD	RA, RAV, RAVL, RTD, M28, M30

Did you know that you can get up to **10 years warranty** with Danfoss?
 ➤ Go to trv.danfoss.com for more information

Product Overview

Radiator thermostats and valves

ENGINEERING
TOMORROW



Domestic Radiator Valves



	Fixed Capacity RAS-C2 + RLV-D	Fixed Capacity RAS-D2 + RLV-D	Pressure Independent RAS-B2 + RLV-D
Energy saving			
Hydronic balancing			
Noise level	 "Revolver" can reduce water hammer if valve is fitted on return	 "Revolver" can reduce water hammer if valve is fitted on return	 Stop noise in radiators through correct balancing
Easy pre-setting	 Easy	 Easy	 Easiest
Comfort level			

Commercial Radiator Valves



	Fixed Capacity RA-FN	Pre-setting RA-N	Pressure Independent RA-Dynamic
Energy saving			
Hydronic balancing			
Noise level			
Easy pre-setting		 Easy	 Easiest
Easy pump optimization		 Easy	 Easiest

Did you know that you can get up to **10 years warranty** with Danfoss?

➤ Go to trv.danfoss.com for more information