

Data Sheet

Ikargo1 Transmitter

Remote Control

The IKARGO1 remote control is highly customizable with many features and accessories. These remote controls also support the operator with an ergonomic design that allows for safe and efficient operation.

Features

- High-sensitivity two-step push button
- Multi-band Radio with Full-Duplex communication
- External removable EEPROM SIM module
- Frequency management against interferences

Benefits

- Highly customizable
- Easy and fast maintenance
- High resistance to impacts
- Improved ergonomics
- Screen display

Applications

- Used in lifting applications
- Used in crane applications

Comprehensive technical literature is online at www.danfoss.com





Technical data

Specification	Value
Stop function	Cat. 3-PLd
Ingress Protection	IP65/NEMA4
Anti-condensation system	N/A
Frequency band	Multi-band (400-930 MHz)
Main mechanisms	Push button (6) / multi-key (1)
Auxiliary mechanisms	N/A
Removable EEPROM	External
Battery model	BT11K
Battery life	8 hours (100% duty cycle)
Operating/storage temperature	-20° to 70° C (-4° to 158° F)
Weight (with battery)	400g
Harness	Hand/shoulder strap
Display	Yes
Cable connection	N/A
Range limiter	Yes
Associated receivers	R06, R13 B, R13 F, R70