



Greyhound™ EHA500



Engineered to power through the toughest conditions

Boston® Greyhound is manufactured with our abrasion, ozone and weather resistant cover and is the ideal, high-pressure air and multipurpose hose for any obstacle in the field. Offered in a large size range expanding from -8 through -64 and maintaining a consistent 600 psi rating across all sizes, this hose is the solution for many markets.

Greyhound is designed for durability at constructions sites, oil fields, mines, steel and paper mills and anywhere a high-pressure air service is needed.



Markets/Applications

- Construction
- Oil field equipment
- Drilling equipment
- Mining
- Rental industry
- Steel
- Paper
- High-pressure air service



Sells Against

- Conti: Ultrabraid® Bull Hose
- Parker: THORO-BRAID
- Gates: Mine Master™ Air Drill 600HT
- Kuriyama: T140AK

Features

- High-pressure capability up to 600 psi
- Pin-pricked synthetic cover
- Heavy-duty abrasion, ozone, and weather resistant cover
- Nitrile blend tube is oil-resistant
- 4:1 safety factor
- Standard tier, price fighting option to Boston Bulldog Gold® H6009


Order Fulfillment

- Made to Stock
- Made to Order



Greyhound EHA500

Heavy duty air hose engineered for high-pressure industrial applications



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Minimum Bend Radius		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kg/m	lbs/ft	mtr	ft
EHA500-08YW-100	12.7	0.50	23.6	0.93	41.0	600	165	2400	65.0	2.56	0.51	0.34	30.5	100
EHA500-12YW-100	19.1	0.75	30.1	1.19	41.0	600	165	2400	95.0	3.74	0.62	0.42	30.5	100
EHA500-16YW-100	25.4	1.00	36.8	1.45	41.0	600	165	2400	125.0	4.92	0.88	0.59	30.5	100
EHA500-20YW-100	31.8	1.25	44.0	1.73	41.0	600	165	2400	160.0	6.30	1.12	0.75	30.5	100
EHA500-24YW-100	38.1	1.50	51.0	2.01	41.0	600	165	2400	190.0	7.48	1.55	1.04	30.5	100
EHA500-32YW-100	50.8	2.00	67.2	2.65	41.0	600	165	2400	225.0	8.86	2.51	1.69	30.5	100
EHA500-40YW-100	63.5	2.50	81.2	3.20	41.0	600	165	2400	315.0	12.40	3.36	2.26	30.5	100
EHA500-48YW-100	76.2	3.00	95.4	3.76	41.0	600	165	2400	380.0	14.96	4.49	3.02	30.5	100
EHA500-64YW-100	101.6	4.00	123.6	4.87	41.0	600	165	2400	510.0	20.08	6.77	4.55	30.5	100

Construction

Tube Oil-resistant nitrile blend

Reinforcement

High-tensile steel wire

Cover Pin-pricked, abrasion, ozone, and weather resistant synthetic rubber

Operating Temperature

-40°F to +200°F
(-40°C to +93°C)

Packaging

50, 100 ft.

Type of couplings

- Boss
- Ground joint
- Air hammer
- Air King
- Danfoss Quick disconnect

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.