

Bulldog® Fuel Delivery H901

Boston by Danfoss Bulldog Fuel Delivery H901 Petroleum Fuel Oil Discharge



Engineered to fuel the future

The H901 Boston® Bulldog fuel oil discharge hose offers a wide application range with RMA Class A material and bio-fuel compatibility.

Boston Bulldog hose is engineered with braided construction that maintains hose structure better than a spiral hose. It comes in lengths of 100 ft to 300 ft and is ideal for fuel oil delivery, petroleum refining, and chemical processing areas.



Markets/Applications

- Marine
- Mining
- Petrochemical/Terminal operations
- Commercial and residential fuel oil delivery



Sells Against

- Continental Versabraid™
- Gates Fuelmaster™ Delivery
- Texcel® TEX-F.O.D.

Features

- Higher abrasion resistance compared to a spiral hose offering
- Meets RMA Class A oil swell requirements decreasing service failures
- Ozone resistant, non-marking, bright red cover provides easy identification
- Lightweight compared to competitor hose
- Double-braided fiber reinforcement with improved bend radius

Order Fulfillment

- Made to Stock

Bulldog Fuel Delivery H901

Fuel oil transfer for residential and/or commercial delivery

Boston by Danfoss Bulldog Fuel Delivery H90116 Petroleum Fuel Oil Discharge 25.4 MM (1.00 IN) DN25 17.2 BAR (250 PSI) -40°C to +82°C (-40°F to +180°F) YYYY/MM/DD Made in USA //-- XXXXX



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	kg/m	lbs/ft	mtr	ft
H90116-150	25.4	1.00	38.1	1.50	17.2	250	69.0	1000	0.68	0.46	91.4	150
H90122-150	34.9	1.38	49.1	1.93	17.2	250	69.0	1000	0.99	0.66	45.7	150
H90124-150	38.1	1.50	52.3	2.06	17.2	250	69.0	1000	1.11	0.75	45.7	150

Construction

Tube Nitrile rubber

Reinforcement

Double fiber braid

Cover Vinyl nitrile rubber

Operating Temperature

-40°F to 180°F
(-40°C to +82°C)

Certifications

RMA Class A

Packaging

150 ft.

Type of couplings

- Reattachable
- Internally expanded permanent attached

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.