



Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without sub sequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.


Industrial Hose in Oil & Gas

reliable solutions that meet your needs

oil & gas


slurry, mud, frac & well service

Bulldog Gold® H6009



- -40°C to +121°C (-40°F to +250°F)
- Up to 83 bar (1,200 psi)
- Nitrile RMA class A tube
- Pin-pricked carboxylate nitrile cover


Kelly Power® Drilling H0377



- -40°C to +121°C (-40°F to +250°F)
- 207 bar (3,000 psi)
- Nitrile/Hypalon tube
- MSHA approved neoprene cover

water & brine


Mink™ EHW150



- -25°C to +70°C (-13°F to +158°F)
- 10.5 bar (150 psi)
- Steel helical wire
- NBR RMA class A cover


chemical transfer

Chemcat® H0523



- -40°C to +80°C (-40°F to +176°F)
- Intermittent
- Up to 21 bar (300 psi)
- FDA compliant
- Meets DIN & ANSI requirements
- UHMW-PE tube with EPDM cover (GN, PR)


Chemcat Flex™ H0599



- -40°C to +121°C (-40°F to +250°F)
- Intermittent
- Up to 21 bar (300 psi)
- FDA compliant UHMW-PE tube
- Corrugated EPDM cover

petroleum suction & discharge

Royalflex® Petroleum H1193




- -29°C to +82°C (-20°F to +180°F)
- Up to 21 bar (300 psi)
- Long length capability
- B20 biodiesel compatible
- High crush & abrasion resistance

Puma® H0363



- -40°C to +82°C (-40°F to +180°F)
- 10.5 bar (150 psi)
- Steel helical wire & anti-static wire
- Vinyl nitrile RMA class A tube & cover


Puma Flex™ EHP519



- -40°C to +82°C (-40°F to +180°F)
- 10.5 bar (150 psi)
- Steel helical wire & anti-static wire
- Vinyl nitrile RMA class A tube & cover
- Corrugated, flat construction


air service

Bulldog Gold® H6009




- -40°C to +121°C (-40°F to +250°F)
- Up to 83 bar (1,200 psi)
- Nitrile RMA class A tube
- Pin-pricked carboxylate nitrile cover

Greyhound™ EHA500



- -40°C to +93°C (-40°F to +200°F)
- 41 bar (600 psi)
- Oil-mist resistant tube
- Abrasion, ozone & weather resistant cover

Bulldog Air™ H6002



- -40°C to +93°C (-40°F to +200°F)
- Up to 28 bar (400 psi)
- Pin-pricked cover
- MSHA approved

proven process
powerful performance