



Bulldog Gold[®] H6009



Engineered to thrive under pressure

Boston[®] Bulldog Gold is the premium solution on the market for high-pressure air and multipurpose applications. Constructed with a multi-wire braided reinforcement this hose offers pressure ratings up to 1,000 psi and is built to withstand the toughest environments in construction, mining, water drilling and more.

Bulldog Gold is offered in 50 and 100 ft. lengths and is approved with a diverse fitting offering providing you the flexibility you need in the field. Additionally, every foot of hose is easily identified by means of permanent branding, making on the job hose selection quicker, easier and safer.

Features

- High-pressure capability up to 1,000 psi
- Pin-pricked carboxylated nitrile cover
- Oil-resistant, nitrile (RMA Class A) tube
- 4:1 safety factor

Order Fulfillment

- Made to Stock



Markets/Applications

- Boring
- Mining
- Fracking industry
- Construction
- Water drilling
- Ship building
- Air-operated drills
- Mining equipment
- Oil and gas exploration
- Air-operated construction equipment



Sells Against

- Gates Black Gold[®] Oilfield Frac
- Parker STINGER[™] II



Bulldog Gold[®] H6009

Provide power to air-operated drills, boring, construction and mining equipment



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	kg/m	lbs/ft	mtr	ft
H600924-100	38.1	1.50	55.6	2.19	41.0	600	165	2400	2.01	1.34	30.5	100
H600932-100	50.8	2.00	69.0	2.72	41.0	600	165	2400	2.95	1.97	30.5	100
H600940-100	63.5	2.50	81.7	3.22	41.0	600	165	2400	3.75	2.50	30.5	100
H600948-100	76.2	3.00	96.0	3.78	41.0	600	165	2400	4.72	3.15	30.5	100
H600964-100	101.6	4.00	128.5	5.06	35.0	500	138	2000	7.97	5.32	30.5	100

Construction

Tube Nitrile (RMA Class A)

Reinforcement

1.00" - 1.25"	1-wire braid
1.50" - 3.00"	2-wire braid
4.00"	3-wire braid

Cover Pin-pricked carboxylated nitrile

Operating Temperature

-40°C to +121°C
(-40°F to +250°F)

Certifications

RMA Class A

Packaging

50, 250, 500 ft.

Type of couplings

- Danfoss TTC/Z series (-20 to -32)
- Union
- Boss male
- Ground joint female
- Air hammer
- Air King
- Danfoss Quick disconnect

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Danfoss Power Solutions
2800 East 13th Street • Ames, IA 50010, USA • Phone: +1 515 239 6000

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.