



Marauder® Heavy Duty EHK007



Engineered for heavy-duty pumping

Boston® Marauder Heavy Duty is built for the delivery of ready mix concrete from the mixer to the construction site. Offered in a large size range, up to 6", and maintaining a constant psi of 1,250, this hose is built to tackle any application. When you need a hose built for rough and demanding conditions, Boston Marauder Heavy Duty is the go-to solution.



Markets/Applications

- For high pressure concrete pumping and placing, used in the end of concrete pump boom
- Heavy duty hose construction for applications needing long lasting durability
- Construction
- Cement placement
- Boom truck



Sells Against

- Continental Allcrete® Wire

Features

- Extremely high abrasion resistance providing an extended hose life
- 20% more flexible than competitive products

Order Fulfillment

- Made to Stock
- Made to Order



Marauder Heavy Duty EHK007

Heavy duty solution for spraying plaster and grout, sand and ready-mix concrete pumping



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Minimum Bend Radius		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kg/m	lbs/ft	mtr	ft
EHK007-32-100	50.8	2.00	70.0	2.76	86.0	1250	200	2900	200	7.87	3.03	2.04	30.5	100
EHK007-40-100	63.5	2.50	88.0	3.46	86.0	1250	200	2900	240	9.45	4.48	3.01	30.5	100
EHK007-48-100	76.2	3.00	102.0	4.02	86.0	1250	200	2900	275	10.83	5.46	3.67	30.5	100
EHK007-64-100	101.6	4.00	130.0	5.12	86.0	1250	200	2900	350	13.78	8.46	5.68	30.5	100
EHK007-80-100	127.0	5.00	155.0	6.10	86.0	1250	200	2900	425	16.73	9.63	6.47	30.5	100
EHK007-96-100	152.4	6.00	180.0	7.09	86.0	1230	200	2900	650	25.59	10.99	7.38	30.5	100

Construction

Tube Abrasion resistant anti-static natural rubber and CBR rubber

Reinforcement

High tensile steel cords

Cover

Abrasion, ozone and weather resistant pin-pricked synthetic rubber

Colors

Black (BK)

Operating Temperature

-40°C to +70°C
(-40°F to +158°F)

Certifications

Meets the requirements of ASME B30.27-2014

Abrasion loss value acc. DIN53516 ≤60mm³

Packaging

MTS: 100 ft.

MTO: 100 ft.

Coil on pallet

Type of couplings

• Victaulic male NPT

Contact coupling manufacturer for attachment procedure and other coupling recommendations