



# SETTINGS



084R9602

Refrigeration and Air  
Conditioning Controls

## AKC 24P2, 084B2028



RI1J9152

<b>AKC 24P2 indstillinger</b> <b>AKC 24P2 Einstellungen</b> <b>Réglages AKC 24P2</b>	<b>Software version 1.1x</b> <b>Software Version 1.1x</b> <b>Logiciel version 1.1x</b>	<b>Adresse (1-120)</b> <b>Address (1-120)</b> -----
Indstillet af: <i>Firma / Person / Dato</i> Set by: <i>Firm / Person / Date</i> Eingestellt von: <i>Firma / Person / Datum</i> Réglé par: <i>Firm / Personne / Date</i>  -----/-----/-----		[ ] = Fabriksindstilling Factory setting Werkseinstellung Réglages d'usine

Level 1,	Level 2,	Level 3,	Settings
DANFOSS AKC 24P2			
Main Function			
	Main Switch Ctrl(1)/Serv(-1)		
	Main Switch	[0]	_____
	Rfg. type 1..23		
	Rfg. type R	[0]	_____
Injection Ctrl. A			
	Inj. Settings		
	Inj. Ctrl. A	[off]	_____
	MOP	[off]	_____
	MOP°C	[0]	_____
	Adv.Inject Settings		
	SH Close K	[4]	_____
	SH min K	[6]	_____
	SH max. K	[10]	_____
	AKV max %	[100]	_____
	PWM s	[6]	_____
	Kp min	[3]	_____
	Kp max	[6]	_____
	Tper. sec	[180]	_____
	Kp P0 A	[1]	_____
	P0 A Lo Range	[-1]	_____
	P0 A Hi Range	[12]	_____
Injection Ctrl. B			
	Inj. Settings		
	Inj. Ctrl. B	[off]	_____
	MOP	[off]	_____
	MOP°C	[0]	_____
	Adv.Inject Settings		
	SH Close K	[4]	_____
	SH min K	[6]	_____
	SH max. K	[10]	_____
	AKV max %	[100]	_____
	PWM s	[6]	_____
	Kp min	[3]	_____
	Kp max	[6]	_____
	Tper. sec	[180]	_____
	Kp P0 B	[1]	_____
	P0 B Lo Range	[-1]	_____
	P0 B Hi Range	[12]	_____