



**AKC 24W2 indstillinger**  
**AKC 24W2 Einstellungen**  
**Réglages AKC 24W2**

**Software version 1.0x**  
**Software Version 1.0x**  
**Logiciel version 1.0x**

**Adresse (1-120)**  
**Address (1-120)**  
 -----

Indstillet af: *Firma / Person / Dato*  
 Set by: *Firm / Person / Date*  
 Eingestellt von: *Firma / Person / Datum*  
 Réglé par: *Firm / Personne / Date*

-----/-----/-----

[ ] = Fabriksindstilling  
 Factory setting  
 Werkseinstellung  
 Réglages d'usine

**Level 1, Level 2, Level 3, Settings**

DANFOSS AKC 24W2

**Main Function**

Main Switch Ctrl(1)/Serv(-1)  
 Main Switch [0] \_\_\_\_\_  
 Cooling(1)/Heating(2)  
 Cool/Heat [1] \_\_\_\_\_  
 Rfg. type 1..19  
 Rfg. type R [0] \_\_\_\_\_

**Capacity Ctrl.**

Cap. Settings  
 Cap. Ctrl. [Off] \_\_\_\_\_  
 Media °C [10] \_\_\_\_\_  
 Media AI °C [50] \_\_\_\_\_  
 Limit °C [4] \_\_\_\_\_  
 NZ K [2] \_\_\_\_\_  
 +Zone K [2] \_\_\_\_\_  
 -Zone K [2] \_\_\_\_\_  
 Adv.Capacity Settings  
 Media Sens [1] \_\_\_\_\_  
 Limit Sens [2] \_\_\_\_\_  
 + Zone s [120] \_\_\_\_\_  
 -Zone s [60] \_\_\_\_\_  
 ++Zone s [30] \_\_\_\_\_  
 --Zone s [30] \_\_\_\_\_  
 Del A min. [10] \_\_\_\_\_  
 Del B min. [10] \_\_\_\_\_  
 Max. Step A [4] \_\_\_\_\_

Max. Step [8] \_\_\_\_\_  
 Ext.Ref. [0] \_\_\_\_\_  
 Ext.Max. K [10] \_\_\_\_\_  
 Max A h/10 [0] \_\_\_\_\_  
 Max B h/10 [0] \_\_\_\_\_  
 Time share [1] \_\_\_\_\_  
 Step mode [1] \_\_\_\_\_  
 DO9 mode [1] \_\_\_\_\_  
 DO9 set°C [20] \_\_\_\_\_  
 DO9 diff K [2] \_\_\_\_\_

**Injection Ctrl. A**

Inj. Settings  
 Inj. Ctrl. A [off] \_\_\_\_\_  
 MOP [off] \_\_\_\_\_  
 MOP°C [0] \_\_\_\_\_  
 Adv.Inject Settings  
 SH Close K [2] \_\_\_\_\_  
 SH Min K [4] \_\_\_\_\_  
 SH Max. K [12] \_\_\_\_\_  
 AKV max % [100] \_\_\_\_\_

**Injection Ctrl. B**

Inj. Settings  
 Inj. Ctrl. B [off] \_\_\_\_\_  
 MOP [off] \_\_\_\_\_  
 MOP°C [0] \_\_\_\_\_  
 Adv.Inject Settings  
 SH Close K [2] \_\_\_\_\_  
 SH Min K [4] \_\_\_\_\_  
 SH Max. K [12] \_\_\_\_\_  
 AKV max % [100] \_\_\_\_\_