




Connecto NA - CSA Power Connection Kits

Danfoss Connecto NA is a family of connection kits for self-regulating heating cables (trace heaters). The Connecto NA connection kits are simple and safe to use, yet faster to install and more cost effective than conventional systems. They can be used with Danfoss:

- PX Pipe Trace Heating Systems
- RX-C Roof and Gutter De-Icing Systems

Product specifications

Benefits <ul style="list-style-type: none"> • Fast and easy to install • Cost savings by reduced assembly time • Great reliability of assembly simplicity • Safe electrical contacting by precise clamp cutting technology • Watch the installation video: http://bit.ly/Connecto-Video Compliance symbols: 	Operating Voltage	Max. 250 V AC
	Current	Max. 16 A
	Ambient Temperature Range	-40 °F to 185 °F / -40 °C to 85 °C
	Operation Temperature Range	-40 °F to 150 °F / -40 °C to 65 °C
	Protection Class	NEMA Type 4X / IP66

Types

Item no.	Product name	Assembly Type	EAN no.
088L0760	Connecto NA-B-PK Power/End Seal Kit	Power connection assembly with End Seal	5703466244517
088L0761	Connecto NA-B-P Power Kit	Power connection assembly	5703466244524
088L0762	Connecto NA-B-S Splice Kit	Splice assembly	5703466244531
088L0763	Connecto NA-B-PS Powered Splice Kit	Powered splice assembly	5703466244548
088L0764	Connecto NA-B-T T-Splice Kit	T-splice assembly	5703466244555
088L0765	Connecto NA-B-PT Powered T-Splice Kit	Powered t-splice	5703466244562
088L0766	Connecto NA-B-X X-Splice Kit	X-splice	5703466244579
088L0767	Connecto NA-B-E Silicone/ End Seal Kit	End seal	5703466244586

ATTENTION. Danfoss Connecto NA may not be put in the gutters when used Roof applications. Must be installed in a dry place.

Kit contents. Danfoss Connecto NA for CSA heating cables with braiding: SLPG-10 (PX-F3), SLPG-15/SLIG-18 (PX-F5), SLPG-25/26 (PX-F8), SLPG-33 (PX-F10).

Ordering Information		Included within each kit						
		Base connection	Threaded cap	Sleeve	Clamping sleeve	Clamping sheet	End cap	Silicone adhesive
088L0760 Connecto NA-B-PK Power connection with end seal		 x1	 x1	 x1	 x1	 x1	 x1	 x1
088L0761 Connecto NA-B-P Power connection		 x1	 x1	 x1	 x1	 x1	—	—
088L0762 Connecto NA-B-S Splice connection kit		 x1	 x2	 x2	 x2	 x2	—	—
088L0763 Connecto NA-B-PS Powered splice kit		 x1	 x2	 x2	 x2	 x2	—	—
088L0764 Connecto NA-B-T T-Connection kit		 x1	 x3	 x3	 x3	 x3	—	—
088L0765 Connecto /NA-B-PT Powered T-Connection kit		 x1	 x3	 x3	 x3	 x3	—	—
088L0766 Connecto NA-B-X X-Connection kit		 x1	 x4	 x4	 x4	 x4	—	—
088L0767 Connecto NA-B-E Silicone end seal (5X)		—	—	—	—	—	 x5	 x1

Connecto NA system installation steps

1. Cut the heating cable straight
2. Push the heating cable in
3. Twist until closed

