

# INSTRUCTIONS TWA NC/S

**TWA-A**  
for Danfoss RA valves

Max. 1 Nm

**NC/S**  
Normally closed and end-switch

Max. 60 °C

Blue/Brown

24 V ~ Thermostat

Green/Green

24 V ~ /0.5 A End Switch

24 V Class III (supply from SELV transformer)

**IP41**