





5.




3.


						Danfoss A/S 6430 Nordborg Denmark
Max. load: 10W/50mA						
<i>Icon™</i> Dial 230V						
		L	N	N	Load NC	Load NO
		220-240V 50-60 Hz				




4.



1.




2.







6.





7.



8.



9.



❄ = 5°C

13657 000 03 Manual Installation WRT Dial 230 F88 IW

ENGINEERING
TOMORROW

Danfoss

Installation & User Guide

Danfoss *Icon*™ Dial

Room Thermostat

VICUX40F/088N3652

www.icon.danfoss.com