

DEVireg™ Plug-in



DEVireg™ Plug-in is an electronic thermostat to be installed in indoor directly to a socket. Plug in design make it easy to install and connect ready-made cables with Schuko

plug like **DEVipeheat 10 V2 or V3**. Used primarily for controlling a lower temperature range as by frost protection. A wire sensor must be used to measure and control the desired temperature.

Benefits:

- Plug in and go
- ON/OFF switch
- LED indicator
- Low temperature area

Standard compliance:

- EN/IEC 60730-1 (general)
- EN/IEC 60730-2-9 (thermostat)

Compliance symbols:



Type	Value
Nominal voltage	220 V- 240V~ 50/60 Hz
Relay:	
Resistive load	16A / 3680W @ 230V
Inductive load	Cos Φ = 0.3 max. 1A
Compatible sensors	NTC 10 k Ω @ 25°C, 3 m.
Hysteresis	\pm 0,5 °C
Temperature range	+3 °C to +15 °C (Default is +5 °C)
Ambient temperature	0° to +50°C
Controller type	1 B
Storage temperature and conditions	-25°C to 60°C, 90% RH non-condensing
IP Class	20
Protection class	Class II - \square
Dimensions	70 x 41,5 x 140 mm
Weight, net	270 g

Types: DEVireg™ Plug-in

Item no.	Product name	Type	EAN no.
140F1134	DEVireg™ Plug-in	Temp. range. +3 °C to +15 °C incl. wire sensor	5703466251232