

DEVireg™ Basic

 Product
is covered
by **EPD***


DEVireg™ Basic is an intuitive programmable timer thermostat, for floor temperature control, complying with Eco design Lot 20, used for controlling electric floor heating elements. The thermostat is designed for fixed installation only. Due to the special designed 2-part construction it fits a wide range of frames in the 55 mm x 55 mm. The thermostat features

a dial for manual temperature setting, feature enabling and intuitive control.

DEVireg™ Basic is fast and intuitive to setup using the in app wizard. It has an energy-saving program - including an optimum start (pre-heat) control ensuring the desired temperature, at the correct time and thereby reducing the heating costs significantly.

Benefits:

- Eco design compliant Lot 20
- Works out of box
- Bluetooth thermostat
- In app setup wizard
- Fit Multiple 55x55 frames
- 7 day, 3 periods programmable
- Sensor failure monitoring
- Adaptive PWM control
- Pre-Heating
- Multilanguage app
- Shine through indicators
- Quick exchange system
- Tested best in class design


Standard compliance:

Radio Equipment Directive

- LVD 60730-1, -2-7 and -2-9
- EMC EN 301 489 -1 and -17
- RF EN 300328

Compliance symbols:



Type	Value
Nominal voltage	220 - 240 V, 50/60 Hz
Standby power consumption, max	0,2 W
Relay: Resistive load Inductive load	16A / 3680W @ 230V Cos Φ = 0.3 max. 1A
Compatible sensors	NTC 15 kΩ @ 25 °C, 3 m. (default)
Regulation	PWM - Pulse Width Modulation
Frost protection	4 °C - 14 °C (default 5 °C)
Temperature range	5 °C to 35 °C (45 °C with break out) (floor)
Cable specification for connector terminals	Max: 1 x 4 mm ² or 2 x 2.5 mm ²
Ball pressure test	75 °C
Pollution degree	2 (domestic use)
Software class	A
Controller type	1 B
Storage temperature and conditions	-25 °C to 60 °C, 90% RH non-condensing
Operating temperatures and conditions	0 °C to 35 °C, 90% RH non-condensing
IP class	21
Protection class	Class II - 
Immunity against voltage surges	Over Voltage Category III
Battery type or Name	Coin battery Manganese Lithium
Dimensions (H/W/D):	85 mm x 85 mm x 20-24 mm (in-wall depth: 22mm)
Weight, net	194 g

Types: DEVireg™ Basic

Item no.	Product name	Type	EAN no.
140F1160	DEVireg™ Basic	Ecodesign programmable thermostat with NTC 15 kΩ @ 25°C, 3 m sensor in box	5703466250372



App:

Accessories

Item no.	Product name	Type	EAN no.
140F1091	Sensor 3 m, 15 kOhm, Santoprene	Wire sensor, 2x0,75 mm ² , NTC 15 kOhm at 25 °C, Ø5x18 mm, black Santoprene (TPV), IP 67	5703466209301
140F1098	Temperature Sensor 10 m NTC 15k Santoprene		5703466210734
19121445	Sensor cable 40 m, 15 kOhm, Santoprene		5703466115015

Connection scheme

