

STL Sales Code Overview

Complete Valves

SSTC - Stop Valves 40 Bar									Spareparts		Packing Gland incl. sealing ⁽¹⁾	Spare part kit, cone	Spare part kit, for bonnet and cap (dismounting set) ⁽²⁾
DN (Inch)	Cap				Handwheel								
	ANG		STR		ANG		STR						
	ANSI	SOC	ANSI	SOC	ANSI	SOC	ANSI	SOC					
15 (½)	148B0906	148B0951	148B0928	148B0959	148B0907	148B0950	148B0929	148B0958	148B4075	148B4060	148B6458	148B6456	148B6454
20 (¾)	148B0908	148B0953	148B0930	148B0961	148B0909	148B0952	148B0931	148B0960					
25 (1)	148B0910	148B0955	148B0932	148B0963	148B0911	148B0954	148B0933	148B0962					
32 (1¼)	148B0912	148B0957	148B0934	148B0965	148B0913	148B0956	148B0935	148B0964	148B4076	148B4062	148B6459	148B6457	148B6455
40 (1½)	148B0914		148B0936		148B0915		148B0937			148B4064	148B6460	148B6469	148B6463
50 (2)	148B0916		148B0938		148B0917		148B0939					148B6470	148B6464
65 (2½)	148B0918		148B0940		148B0919		148B0941						
80 (3)	148B0920		148B0942		148B0921		148B0943			148B4077	148B4065	148B6461	148B6450
100 (4)	148B0922		148B0944		148B0923		148B0945		148B4066		148B6451		148B6466
125 (5)	148B0924		148B0946		148B0925		148B0947		148B4078	148B4067	148B6462	148B6452	148B6467
150 (6)	148B0926		148B0948		148B0927		148B0949					148B6453	148B6468

Complete Valves

	SReg-SA Cone Type A		SReg-SB Cone Type B		SSCA		SCHV		SFIA Complete Valves without filter element		Filters							Spare Parts			
	Cap		Cap		Cap						FIA: Filter insert-plain				FIA: Filter insert-pleated			Spare part kit SREG cone	Spare part kit SSCA/ SCHV		
DN (Inch)	ANG	STR	ANG	STR	ANG	STR	ANG	STR	ANG	STR	100µ	150µ	250µ	500µ	150µ	250µ	500µ				
	ANSI	ANSI	ANSI	ANSI	ANSI	ANSI	ANSI	ANSI	ANSI	ANSI											
15 (½)	148B7768	148B7769	148B7778	148B7779					148B7750	148B7751	148H3122	148H3124	148H3126	148H3128	148H3303	148H3363		148B7795			
20 (¾)	148B7770	148B7771	148B7780	148B7781					148B7752	148B7753											
25 (1)	148B7772	148B7773	148B7782	148B7783					148B7754	148B7755											
32 (1¼)	148B7774	148B7775	148B7784	148B7785					148B7756	148B7757	148H3123	148H3125	148H3127	148H3129	148H3304	148H3269		148B7796			
40 (1½)	148B7776	148B7777	148B7786	148B7787					148B7758	148B7759											
50 (2)					148B7800	148B7801	148B7808	148B7809	148B7760	148B7761	148H3157	148H3130	148H3138	148H3144	148H3179	148H3184	148H3189		148B7816		
65 (2½)					148B7802	148B7803	148B7810	148B7811	148B7762	148B7763		148H3131	148H3139	148H3145	148H3180	148H3185	148H3190		148B7817		
80 (3)					148B7804	148B7805	148B7812	148B7813	148B7764	148B7765		148H3119	148H3120	148H3121	148H3181	148H3186	148H3191		148B7818		
100 (4)					148B7806	148B7807	148B7814	148B7815	148B7766	148B7767		148H3132	148H3140	148H3146	148H3182	148H3187	148H3192		148B7819		

⁽¹⁾ Suitable for SREG as well, but not suitable for SSCA
⁽²⁾ Spare parts for DN 15-100 are suitable for SFIA 15-100

Danfoss A/S
Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

ENGINEERING
TOMORROW

