



Premium 4-wire spiral

The best selling **GH493 MatchMate®** hydraulic hose

Pressures, temperatures and abrasion resistance all **exceed industry standards**, 24% higher pressures on average.



Standards/ Certificates:

Meets or exceeds: SAE 100R12 | EN 856 R12 |
EN 856 4SP (-8 to -12) | ISO 18752 | ISO 3862 R12

Sizes and pressure (bar/psi):

-06 (448/6500)	-16 (350/5100)
-08 (415/6000)	-20 (310/4500)
-10 (415/6000)	-24 (275/4000)
-12 (380/5500)	-32 (275/4000)

Operating temperature:

-40°C to +127°C (-40°F to +260°F)

Available fittings:



45 Series

Crimp fittings with Dura-Seal technology provide Class 0 cool down leakage.

Inner Tube:

Synthetic rubber tube

Reinforcement:

4 wire spiral

Cover:

DURA-TUFF™ synthetic rubber

Typical Application:

For very high pressure hydraulic lines subjected to pressure surges and flexing. Typical applications include construction, mining, farming, and high performance industrial equipment.

MSHA approved
USCG approved
DNV
ABS