

## Solenoid valve

Type EV310A



520B1034

520B1034

<p><b>A</b></p>	<p><b>B</b> NC <b>C</b> NO</p>	<p><input checked="" type="checkbox"/></p> <p>&gt;50 mesh (&lt;297 Microns)</p> <hr/> <p><input checked="" type="checkbox"/></p> <p>ON OFF</p> <p>24h</p>
<p><b>1</b></p>	<p><b>2</b></p>	<p><b>3</b></p> <p>ID</p>
<p><b>4A</b></p>	<p><b>5A</b></p> <p>360° MAX XMM ±0.05</p>	<p><b>6A</b></p> <p>360° MAX XMM ±0.05</p>
<p><b>7A</b></p>	<p><b>8A</b></p>	<p><b>9A</b></p>

Імпортер: ТОВ з іі "Данфосс ТОВ" 04080, Київ 80, п/с 168, Україна

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

4B

5B

4C

5C

6BC

7BC

8BC

2.6 Nm ± 0.2 Nm

9B

9C

10

1.4 Nm ± 0.3 Nm

11

55 Nm ± 5 Ncm

12

13

MTP  
Bar

DN	Max. Working Pressure (MWP) [bar]	Max. Test pressure (MTP) [bar]
1.2 NC	20	30
1.2 NO	13	19.5
1.5 NC / FL	12	18
1.5 NO	7	10.5
2 NC	8	12

EN 60730-2-8