

Installation guide

Solenoid valve

Type EV220B 15 - EV220B 50

032R9274

032R9274

<p>(A)</p>	<p>(B)</p>	<p>☑</p> <p>≥ 50 mesh (≤ 297 microns)</p> <p>☑</p> <p>ON</p> <p>OFF</p>
<p>1</p>	<p>2</p>	<p>3</p> <p>SOLENOID VALVE CAP BY SCREW 1.50 x 1.2 8 INCHES 2003030 MADE IN DENMARK</p> <p>SOLENOID VALVE CAP BY SCREW 1.50 x 1.2 8 INCHES 2003030 MADE IN DENMARK</p>
<p>4A</p> <p>OFF</p>	<p>5A</p>	<p>6A</p> <p>CLICK</p>
<p>4B</p> <p>OFF</p>	<p>5B</p>	<p>6B</p>

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

<p>7</p>	<p>8</p>	<p>9</p>
<p>10</p>	<p>11</p>	<p>12</p>
<p>13</p>	<p>14</p>	<p>15</p>

16

DN	Material	Max. working pressure (MWP)	Max. test pressure (MTP)
		[bar]	[bar]
15-25 NC	EPDM/NBR	16	20
32-50 NC	EPDM/NBR	12	16
15-50 NC	FKM	10	16
15-50 NO	EPDM/NBR/FKM	10	16

EN 60730-2-8

Visit www.products.danfoss.com for further technical data
 Para más información, visite www.products.danfoss.es
 Rendez-vous sur le site www.products.danfoss.fr pour plus de données techniques