



Sales Memo

from Danfoss Heating Controls - PL03

Date: 2009 - 10 - 09

Cancellation of TRV products

Description

Under a clean up process in the TRV business, it has been decided that following Code numbers are going to be cancelled.

Sales information

Material	Description	PLC	Stat no.
003L0099	Drain-off tail piece Asm. GB	034	3997
003L0247	Service set RLV-KD	223	3979
003L0254	RLV-KD Press-fit 1/2" Straight	223	3487
003L0255	RLV-KD Press-fit 3/4" Straight	223	3487
003L0256	RLV-KD Press-fit 1/2" Angle	223	3487
003L0257	RLV-KD Press-fit 3/4" Angle	223	3487
003L6042	AVDO "OEM"		
003L6047	AVDO "OEM" (grey spring)	127	3252
003L6052	AVDO "OEM" (blue spring)	127	3252
003L6120	AVDO 15 L Industrial pack	127	3251
013G0370	RA-N SERIE 3 INTEGRATED VALVE	221	3132
013G0371	RA-U SERIE 3 INTEGRATED VALVE	221	3131
013G0480	INDBYGNINGSVENTIL		
013G1519	Flowswitcher 1 1/4 for BIV	034	3997
013G2360	Built in valve RA-N V & N	221	3132
013G2578	RA 2578 MAX-BEGRÆNSET	016	3172
013G2632	RA-Hvid Snap FF Celcius Skala	016	3209
013G3035	RA-N 20 VALVE BODY SMS	015	3161
013G3110	PLAST.FITT.	034	3997
013G3130	RA-N 10, straight w. low noise nipple	015	3161
013G3151	RA-N 10 SN	015	3193
013G3153	RA-N 15 SN	015	3193
013G3154	RA-N 15 SN	015	3193
013G3161	S-OFF VALVE DN10 V	223	3990
013G3162	S-OFF VALVE DN10 L	223	3990
013G3163	S-OFF VALVE DN15 V	223	3990
013G3164	S-OFF VALVE DN15 L	223	3990
013G3190	HC, RA-FN A 33 / RLV 45- Axial	015	3162
013G3191	HC, RA-FN A 33 / RLV 45- Radial	015	3162
013G3219	RAS-D + RA 15/6 T		
013G3221	RA 15/6T Lance valve	015	3196
013G3222	RA 15/6T Lance valve	015	3196

013G3256	RA-FNE 15 VALVE (SPEC.)	015	3362
013G3260	RA 15/6T BY-PAS	015	3196
013G3312	RA BUILT-IN VALVE M22X1,5	221	3198
013G3321	RA-N DN 10 SIS ANGEL VALVE	015	3161
013G3346	RA-KW Coupling Set incl. RAE Sensor.	022	3205
013G3723	ra-un 15 v (delta seal)	015	3164
013G3724	ra-un 15 l (delta seal)	015	3164
013G4082	VHS Vasco S inox	016	3128
013G4084	VHS Vasco S pergamon	016	3128
013G4086	VHS Vasco S RAL 9016	016	3128
013G4670	VHS-U væg		
013G4677	VHS sæt 1/2" vinkel		
013G4678	VHS sæt , RAS-D, 1/2" vinkel		
013G4679	VHS sæt, 1/2" lige		
013G4680	VHS-U gulv		
013G4687	VHS afdækning firkant, vinkel, PPO		
013G4688	VHS afdækning firkant, lige, PPO		
013G4690	VHS 15 w/reserve direction of flow		
013G4746	RAS-D+VHS-UN Angle+round cover, RAL 9016	016	3367
013G4747	VHS		
013G4752	RAS-D + VHS 15 Straight + cover, chrome	016	3367
013G4756	RAS-D + VHS-UN 15 Angle + cover,RAL 9016		
013G4757	VHS 15 angle + cover, RAL 9016	015	3276
013G4920	IBV 220 for service	221	3132
013G4925	VHS brace for cover	223	3300
013G5001	RA handwheel, chrome	222	3363
013G5004	K handwheel, chrome	222	3363
013G5043	RAW-C 5043, FF (Light grey 7035)	016	3187
013G5044	RAW-C 5044, FF (Black)	016	3187
013G5045	RAW-C 5045, FF (Anthracite 7016)	016	3187
013G5046	RAW-C Light grey RAL 7035	016	3186
013G5047	RAW-C Black RAL 9005	016	3186
013G5048	RAW-C Anthracite grey RAL 7016	016	3186
013G5049	RAW-C Telegrey RAL 7047	016	3186
013G5050	RAS-C UK	015	3221
013G5053	RAW-C FF, RAL 9016 Remote Sensor		
013G5055	RAS-C UK	015	3221
013G5061	RAS-C IF, white snap, limitation	016	3225
013G5063	BIV-RLV-RAE packing, Straight	016	3324
013G5064	BIV-RLV-RAE packing, Angle	016	3324
013G5070	REMOTE SETTING SENSOR 10M CAP.TUBE	016	3174
013G5072	REMOTE SETTING SENSOR 12M CAP.TUBE	016	3174
013G5085	REMOTE SETTING SENSOR 5M CAP.TUBE GREY	016	3174
013G5088	REMOTE SETTING SENSOR 8M CAP.TUBE GREY	016	3174
	REMOTE SETTING SENSOR 8M CAP.TUBE		
013G5098	YELLOW	016	3174
013G5150	RAS COMBI UK.	015	3220
013G5155	RAS COMBI UK.	015	3220
013G5165	REMOTE SETTING SENSOR 5M CAP.TUBE BEIGE	016	3174
013G5168	REMOTE SETTING SENSOR 8M CAP.TUBE BEIGE	016	3174
013G5188	REMOTE SETTING SENSOR 8M CAP.TUBE GREY	016	3174
013G5452	FE Remote Temperature Adjuster Special	221	3297

013G5472	RA 5062 WITH SUN/MOON INDICATION	016	3174
013G6241	Partnerclip for visually impaired	034	3997
013G6285	RA-FS, Straight w. 15 mm fittings (Ni)	015	3221
013G6286	RA-FS, Straight w. 8-10 mm fittings (Ni)	015	3221
013G7372	FITTING WITHOUT NICKEL Ø18	034	3997
013G9360	INDBYGNINGSVENTIL NJ	221	3132
013G9361	INDBYGNINGSVENTIL UJ	221	3131
013G9370	RA-N SERIE 3 INTEGRATED VAVLE	221	3132
013G9371	INTEGRATED VAVLE	221	3132
013G9406	RA-N 20 Straight valve body	015	3161
013G9407	RA-N 25 Angle valve body	015	3161
013G9409	RA-N 10 UK VALVE BODY	015	3161
013G9411	RA-N 20 UK VALVE BODY	015	3161
013G9412	RA-N10 R. MOUNT. VALVE BODY	015	3195
013G9413	RA-N10 L. MOUNTED VALVE BODY	015	3195
013G9588	BUILT-IN VALVE RA-U SERIE 3	221	3131
013G9589	BUILT-IN VALVE RA-U	221	3131
013G9710	013G5010 - RAW IF		
013L3191	VHS anglecover with mounting brace		
013L3192	VHS straightcover with mounting brace		
013L3688	VHS-UN 15 Straight + cover, RAL 9016		
013L3689	VHS-UN 15 Angle + cover, RAL 9016		
013X3179	AFZINKFRI PAKD.	034	3901
013X3199	IBV 390 M22	221	3132
013X3203	RA 2000 Remote, 2m Special with SDA	016	3174
013X3209	FE-FF Sensor in RAL 7011		
013X3211	Grå 2*2 meter	016	3174
013X3212	RAW 5010 Special	016	3186
013X3246	RAW IF, MIN (9016)	016	3186
013X3253	RA-UN 15 UK w/o nipple and union nut	015	3164
013X3259	FED-IF 2+13 m	224	3316
013X3270	EXTENTION	034	3997
013X3275	FEV-FF (RAL 7035)	224	3319
013X3281	FE grå 2 mtr		
013X3282	RA-5062 REMOTE SETTING SENSOR w.2 m cap.		
013X3285	RA-5065 Remote setting sensor with 5 m	016	3174
013X3290	RAW-C, IF black grey RAL 7021	03	
013X3295	FEV-FF Climate Controller, Heating 2+3m	224	3319
013X3297	FED-FF Climate Control 2+2+3m	224	3316
013X3298	RA-FN 10 A, w/o cv-plug	015	3162
013X3299	RA-FN 15 A, w/o cv-plug	015	3162
013X3305	TwA-Z 24V NC 2,5 m cable	642	3306
013X3314	RAS-C Remote Sensor, 4m	016	3294
013X3318	Remote adjuster, 5m w. Celsius-scale	016	3174
192F4112	RA-K 12-15 mm Combi	015	3168
192F4113	RA-KE 15 mm Combi	015	3168
192F4114	RA-KE 18 mm Combi	015	3168
192F4118	RA-KE 18 mm Combi	015	3168
193B0095	Inpack code number No. 1	016	3179
193B0096	Inpack code number No. 2	016	3179
013G7170	RA-N VALVE ACC. FOR UNIVERSALRADIATOR	221	3132
003L1016	FJVR Valve body L, GB		

013G0251	VALVE BODY RIGHT MOUNTED	015	3195
013G0252	VALVE BODY LEFT MOUNTED	015	3195
013G3051	RA-N DN 10 SIS UK VALVE	015	3161
013G3219	RAS-D + RA 15/6 T		
013G3224	RA 15/6T Valve body	015	3196
013G3225	RA-FN 10/20 Valve	015	3162
013G3230	RA-FN 15 FL.PACK	015	3162
013G3249	RA-FN 15 UK	015	3162
013G3251	RA-U 10 UK VALVE BODY	015	3164
013G3253	RA-U 15 UK VALVE BODY	015	3164
013G3258	RA 15/6T VALVE BODY	015	3196
013G3279	RA 15/6T Lance valve	015	3196
013G3280	RA 15/6T Lance valve	015	3196
013G3281	RA-FR 15 UK W/15MM	015	3194
013G3283	RA-FR 15 UK W/8-10MM	015	3194
013G3326	RA-N 15 valve	015	3161
013G3327	RA-N 15 VALVE	015	3195
013G3328	RA-N 15 valve	015	3195
013G3345	RA-KEW Coupling Set incl. RAE Sensor	022	3205
013G3743	RA-UN 15 UK (delta seal)	015	3164
013G4217	RA-FN 15 Straight Ext. thread	015	3162
013G4219	RA-FN 15 UK	015	3162
013G4232	RA-N 15 A without CEN	015	3161
013G4233	RA-N 15 S without CEN	015	3161
013G4234	RA-N 15 "UK" without CEN	015	3161
013G4235	RA-N 15 side valve without CEN	015	3161
013G4236	RA-N 15 side valve without CEN	015	3161
013G4243	RA-FN 15 (013G0143 in I-pack)	015	3162
013G4244	RA-FN 15 (013G0003 in I-pack)	015	3162
013G4245	RA-FN 15 (013G0004 in I-pack)	015	3162
013G4799	VHS-cover, angle version "Gold"	223	3300
013G4800	VHS-cover, straight version "Gold"	223	3300
013G5050	RAS-C UK	015	3221
013G5055	RAS-C UK	015	3221
013G5129	RAS-D IF "Gold"	016	3388
013G5150	RAS COMBI UK	015	3220
013G5155	RAS COMBI UK	015	3220
013G7031	RA-N 10 PASSIV	015	3161
013G7032	RA-N 10 PASSIV	015	3161
013G7033	RA-N 15 PASSIV	015	3161
013G7034	RA-N 15 PASSIV	015	3161
013G7035	RA-N 20 PASSIV	015	3161
013G7036	RA-N 20 PASSIV	015	3161
013G7037	RA-N 25 PASSIV	015	3161
013G7038	RA-N 25 PASSIV	015	3161
013G7151	RA-N 10 PASSIV	015	3161
013G7153	RA-N 15 PASSIV	015	3161
013G7155	RA-N 20 PASSIV	015	3161
013G7291	RA-N 10 PASSIV.	015	3195
013G7292	RA-N 10 PASSIV.	015	3195
013G7293	RA-N 15 PASSIV.	015	3195
013G7294	RA-N 15 PASSIV.	015	3195

013G8011	VALVE RA-N 15 WITH NPT THREAD	015	3161
013L0285	Compression fittings ø10 1/2"	034	3997
013L3263	RTD-K W/SHORT TAILPIECE	015	3137
130-001	1/2" Straight Pattern THZST Valve NPT	755	3475
130-002	3/4" Straight Pattern THZST Valve NPT	755	3475
130-003	1" Straight Pattern THZST Valve NPT	755	3475
130-004	1-1/4" Straight Pattern THZST Valve NPT	755	3475
130-009	1/2" Angle Pattern THZAT Valve NPT	755	3475
130-010	3/4" Angle pattern THZAT Valve NPT	755	3475
130-011	1" Angle Pattern THZAT Valve NPT	755	3475
130-012	1-1/4" Angle Pattern THZAT Valve NPT	755	3475
130-017	1/2" Rev. Angle Pattern THZRT Valve NPT	755	3475
130-018	3/4" Rev. Angle Pattern THZRT Valve NPT	755	3475
130-019	1" Rev. Angle Patte	755	3475
EHE0200136	Wolseley (Comfort br	755	3474
EHE0200137	Wolseley (Alliance)	755	3474
EHE0200138	1/2" Straight FN "DI	755	3475
EHE0200139	1/2" Angle FN "DIN"	755	3475
EHE0200140	1/2" Straight FN "NF	755	3475
EHE0200141	1/2 Straight FN "NF"	755	3475
EHE0200142	1/2" Angle FN "NF"	755	3475
EHE0200143	1/2 Angle FN "NF"	755	3475
EHE0200144	1/2 Rev. angle FN "D	755	3475
EHE0200145	1/2 Rev. angle FN "D	755	3475
EHE0200146	Valve pre-set 15 rev	755	3476
EHE0200147	Pre-set 15 straight	755	3476
EHE0200148	Valve pre-set 15 ang	755	3476
EHE0200149	Lockshield Valve straight RLV-S		
EHE0200150	Lockshield Valve angel RLV-S		
EHE0200151	H-piece Valve RLV-KS Straight		
EHE0200152	H-piece Valve, RLV-KS Angel		
003L0370	RLV-KS 1/2" Straight		
003L0371	RLV-KS 3/4" Straight		
003L0372	RLV-KS 1/2" Angle		
003L0373	RLV-KS 3/4" Angle		
013G3098	3/8" ELBOW		

Ordering

The code numbers will not be produced anymore, but the stock will still be available.

Technical support

Dennis Thaysen Jensen
Marketing Engineer
Danfoss A/S, Silkeborg Factory,
Haarupvaenget 11, DK-8600 Silkeborg
Phone: +45 7488 8018
E-mail: F39701@danfoss.com