


Data Sheet

LX Mat for Electric Floor Heating Applications

General Information



Danfoss LX DUAL ADHESIVE electric floor heating mats are an affordable luxury that brings warmth to life. It's a proven technology that's safe, reliable and energy efficient. The unique adhesive system saves 70% on installation time.

- Pre-applied heating cable
- Dual adhesive backing
- Single point connection
- Twin conductor cable
- Eliminates EMF's (Electromagnetic fields)
- Customize mat on the job site
- Safety approved for wet locations
- Genuine twenty year non-prorated warranty

Technical Data

Typical Applications:	Plywood Subfloor, Concrete Subfloor, Engineered Wood, Laminate, Tile Floor, Stone Floor
Mat Construction:	Thermoplastic polymer coated fiberglass self-adhesive backing
Cable Construction:	Twin conductor
Rated Voltage:	120V, 240V
Output:	12W/ sq. ft. (130W/m ²)
Heating Element Size:	5 ft. (1.5m) to 72.5 ft. (22m) long x 2 ft. (60cm) wide
Cold Lead:	10 ft. (3.0 m)
Bending Radius:	Minimum 3/4 inch (19 mm)
Cable Diameter:	3/16 inch (4.8 mm)
Conductor Insulation:	Teflon™ FEP
Outer Insulation:	PVC
Max. Temperature:	212°F (100°C)
Min. Installation Temp:	50°F (10°C)

See power lead label for NEC connection color code.

Ordering Information LX Mats (120V, 240V)

- All mats are 2 feet in width
- Power leads are 10 feet in length
- Watt output of the 240V mats are reduced by 25% when operated at 208V (9W/sq.ft.)
- Floor sensor conduit is included
- Contactor or Power Module is required for loads exceeding 15 amps on a single thermostat

Part No.		Length (feet)	Area (sq. ft.)	Amps		Watts	Ohms	
120V	240V			120V	240V		120V	240V
088L3150	-	5.0	10	1.0	-	120	120	-
088L3151	-	7.5	15	1.5	-	180	77.8	-
088L3152	-	10.0	20	2.0	-	240	61.3	-
088L3153	-	12.5	25	2.5	-	300	48.0	-
088L3154	-	15.0	30	3.0	-	360	10.0	-
088L3155	088L3175	17.5	35	3.5	1.8	420	34.7	137.1
088L3156	088L3176	20.0	40	4.0	2.0	480	30.0	121.3
088L3158	088L3177	25.0	50	4.9	2.5	600	24.6	97.6
088L3160	088L3178	30.0	60	6.0	3.0	720	20.4	81.1
-	088L3179	35.0	70	-	3.5	840	-	69.8
-	088L3180	40.0	80	-	4.0	960	-	60.6
-	088L3181	45.0	90	-	4.5	1,080	-	54.1
-	088L3182	50.0	100	-	5.0	1,200	-	48.8
-	088L3183	55.0	110	-	5.5	1,320	-	44.3
-	088L3184	60.0	120	-	6.0	1,440	-	40.7
-	088L3185	72.5	145	-	7.3	1,750	-	32.6

Thermostats

Part No.	Description
088L5140	LX205T WIFI Touch Screen Thermostat (Programmable)
088L5136	LX205T Touch Thermostat (Programmable)
088L5130	LX Thermostat with Floor & Air Sensor (Programmable)
088L5137	LX205 Thermostat (Non-Programmable)

Note: All thermostats include a floor sensor with a 10 foot lead.

Accessories

Part No.	Description
088L3008	Replacement floor sensor for LX Thermostat Models 008L5130, 088L5132, 088L5133 only
ETF-110/99C	Replacement Thin Floor Sensor (10K Ω) for Thermostat
088L0014	LX Repair Kit (includes crimp connectors, repair wire, heat shrink tubes)
19809099	Sensor Conduit (8 feet)
088L0028	Little Buzzer - Continuity Alarm

Warranty

Genuine twenty year comprehensive extended warranty against defects in material, design, and workmanship.

Technical Services

For technical questions, please contact Danfoss Heating Division North America at **1-888-DANFOSS (326-3677)**. More information on Danfoss Electric Heating products is available at **www.LX.Danfoss.com**.

Danfoss can accept no responsibility for possible errors in catalogs, brochures, other printed materials, and website information. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alteration can be made without subsequent changes being necessary in specifications already agreed upon. All trademarks in this material are property of the respective companies. Danfoss and Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



Danfoss
 Tel: 1-888-DANFOSS (326-3677)
 option #3 for Heating
 Fax: 416-352-5981
 www.LX.Danfoss.com

Danfoss LX
 BRINGING WARMTH TO LIFE