

Electrical Spare Parts for Danfoss Light Commercial Compressors

	NEW Danfoss Model No.	Voltage/ Phase/ Frequency	HS/LS torque	NEW Danfoss Single Packed Code No. ³	Start relay code no.	Start capacitor code no.	Run capacitor code no.	Protector code no.
R-134a	B38H5L	110/1/60	HS	123B8110	—	—	—	—
	GUY60NRb	115/1/60	HS	123B1301	123B9136	123B9309	—	123B9502
	GL99ADa	115/1/60	HS	123B1161	123B9102	N/A	N/A	123B9471
	GUY80NRb	115/1/60	HS	123B1303	123B9118	123B9309	N/A	123B9498
	GPY12RDa	115/1/60	HS	123B1580	123B9134	123B9314	N/A	123B9494
	GP14FE	115/1/60	HS	123B1163	123B9134	N/A	N/A	123B9494
	GPY14NGa	220-240/1/60	HS	123B1313	123B9136	123B9316	—	123B9502
	GP14FE	115/1/60	HS	123B1163	123B9134	N/A	N/A	123B9494
	GLY12NRa	115/1/60	HS	123B1304	123B9122	123B9314	N/A	123B9491
	B38G5L	110-115/1/60	LS	123B8126	123B9182	123B9322	N/A	123B9571
	GL80TG	200-230/1/ 50/60	HS	123B1528	123B9119	123B9312	N/A	123B9470
	GLY80RDa	115/1/60	HS	123B1572	123B9122	123B9313	N/A	123B9472
	GL80TE	115/1/60	HS	123B1575	123B9122	123B9318	N/A	123B9467
	GPY12RDa	115/1/60	HS	123B1580	123B9134	123B9314	N/A	123B9494
	GLY12RRa	115/1/60	HS	123B1601	123B9134	123B9318	N/A	123B9491
	GPY14RDa	115/1/60	HS	123B1584	123B9138	123B9314	N/A	123B9496
	GPY16RDa	115/1/60	HS	123B1588	123B9138	123B9314	N/A	123B9496
	GP16TG	220-240/1/ 50/60	HS	123B1714	123B9118	123B9316	N/A	123B9482
	GX23TG	208-230/1/60	HS	123B1548	123B9134	123B9316	N/A	123B9494
	GS26TGv	208-230/1/60	HS	123B1550	123B9146	123B9304	N/A	123B9507
GS30TGv	208-230/1/60	HS	123B1553	123B9147	123B9304	123B9205	123B9507	
GS34TFv	208-230/1/60	HS	123B1590	123B9147	123B9304	123B9205	123B9509	
R-404A	ML60FR	115/1/60	HS	123B2143	—	—	—	—
	ML45FR	115/1/60	HS	123B2160	123B9136	123B9309	N/A	123B9499
	MLY60LDa	115/1/60	HS	123B2144	123B9118	123B9313	N/A	123B9482
	ML80FR	115/1/60	HS	123B2146	123B9129	123B9318	N/A	123B9494
	MPT12LD	115/1/60	HS	123B2152	123B9141	123B9314	123B9215	123B9527
	MPT14LD	115/1/60	HS	123B2155	123B9143	123B9314	123B9227	123B9496
	MX21FG	208-230/1/60	HS	123B2131	123B9156	123B9302	N/A	123B9472
	MS26FFv	208-230/1/60	HS	123B2157	132B9153	123B9304	123B9207	123B9529
	MX21FGa	200-230/1/ 50-60	HS	123B2186	—	—	—	—
	MS34FFv	208-230/1/60	HS	123B2174	123B9156	123B9304	123B9207	123B9536
	MLY60RDa	115/1/60	HS	123B2527	123B9122	123B9313	N/A	123B9491
	MLY80RDa	115/1/60	HS	123B2530	123B9134	123B9314	N/A	123B9494
	MLT12RR	115/1/60	HS	123B2542	—	—	—	—
	MPT14RF	230/1/60	HS	123B2543	—	—	—	—
	MX18TGa	208-230/1/60	HS	123B2541	123B9159	123B9304	123B9203	123B9496
	MX18TE	115/1/60	HS	123B2545	123B9110	123B9324	123B9230	123B9714
	MX21TGa	208-230/1/60	HS	123B2714	123B9161	123B9302	123B9207	123B9496

¹Horsepower ratings are nominal. Danfoss recommends sizing compressors based on cooling capacity requirements.

²Capacity at ASHRAE conditions below. For other conditions and/or speeds, check Coolselector or contact Danfoss.

³Code no. contains compressor and required electrical and non-electrical accessories. For standard code no., change "B" to "F."

Full range of models (refrigerant, capacity, and voltage codes) available. Check Coolselector or contact Danfoss.

Full range of models (refrigerant, capacity and voltage codes) available.

Check Coolselector or contact Danfoss.

Test conditions
Condensing temperature
Evaporator temperature
Ambient and suction gas temperature
Liquid temperature



www.choose.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogs, brochures, and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.