

ENGINEERING  
TOMORROW

*Danfoss*

Danfoss X-tra Collection™

## Designer radiator thermostats for designer homes



### 4 styles

to choose from.  
When you combine the  
simplicity of living design®  
with the flexibility of the  
Danfoss X-tra Collection™ –  
it is really all it takes.

[heating.danfoss.com](http://heating.danfoss.com)

# Standard valves

## RAX Room Temperature Sensor

<b>White</b> RAL 9016	013G6070
<b>Black</b> RAL 9005	013G6075
<b>Inox</b>	013G6171
<b>Chrome</b>	013G6170



## RTX Return Temperature Limiter

<b>White</b> RAL 9016	013G6090
<b>Inox</b>	013G6191
<b>Chrome</b>	013G6190



## VHX-MONO (straight) for standard connections

<b>White</b> RAL 9016	<b>RAX</b> 013G4284	<b>RTX</b> 013G4384
<b>Chrome</b>	<b>RAX</b> 013G4282	<b>RTX</b> 013G4382



## VHX-MONO (angle) for standard connections

<b>White</b> RAL 9016	<b>RAX</b> 013G4287	<b>RTX</b> 013G4387
<b>Chrome</b>	<b>RAX</b> 013G4285	<b>RTX</b> 013G4385



## VHX-DUO (straight) for 50 mm connections

<b>White</b> RAL 9016	<b>RAX</b> 013G4278	<b>RTX</b> 013G4378
<b>Chrome</b>	<b>RAX</b> 013G4276	<b>RTX</b> 013G4376



## VHX-DUO (angle) for 50 mm connections

<b>White</b> RAL 9016	<b>RAX</b> 013G4281	<b>RTX</b> 013G4381
<b>Chrome</b>	<b>RAX</b> 013G4279	<b>RTX</b> 013G4379



# Accessories

## Copper fittings

<b>Cu</b> ½x10mm	013G4192
<b>Cu</b> ½x12mm	013G4193
<b>Cu</b> ½x14mm	013G4194
<b>Cu</b> ½x15mm	013G4195
<b>Cu</b> ½x16mm	013G4196



## PEX and AluPEX fittings

<b>PEX</b> ½x12x1,1mm	013G4197
<b>PEX</b> ½x15x2,5mm	013G4199
<b>PEX</b> ½x16x2mm	013G4198
<b>AluPEX</b> ½x16x2mm	013G4200



## Pipe set

½" nipple connection	013G3127
----------------------	----------



## Heating element with stay for VHX-Duo (angle)

<b>Stay</b>	013G4166
<b>150 watt</b> chrome	013G4167
<b>300 watt</b> chrome	013G4168
<b>600 watt</b> chrome	013G4169



## Wall rosettes for 50mm connections (single set)

<b>White</b> RAL 9016	013G3128
<b>Chrome</b>	013G3129
<b>Inox</b>	013G3131

