

ENGINEERING
TOMORROW

Danfoss

Danfoss X-tra Collection™

Designer radiator thermostats for designer homes



4 styles

to choose from.
When you combine the
simplicity of living design®
with the flexibility of the
Danfoss X-tra Collection™ –
it is really all it takes.

heating.danfoss.com

Standard valves

RAX Room Temperature Sensor

White RAL 9016	013G6070
Black RAL 9005	013G6075
Inox	013G6171
Chrome	013G6170



RTX Return Temperature Limiter

White RAL 9016	013G6090
Inox	013G6191
Chrome	013G6190



VHX-MONO (straight) for standard connections

White RAL 9016	RAX 013G4284	RTX 013G4384
Chrome	RAX 013G4282	RTX 013G4382



VHX-MONO (angle) for standard connections

White RAL 9016	RAX 013G4287	RTX 013G4387
Chrome	RAX 013G4285	RTX 013G4385



VHX-DUO (straight) for 50 mm connections

White RAL 9016	RAX 013G4278	RTX 013G4378
Chrome	RAX 013G4276	RTX 013G4376



VHX-DUO (angle) for 50 mm connections

White RAL 9016	RAX 013G4281	RTX 013G4381
Chrome	RAX 013G4279	RTX 013G4379



Accessories

Copper fittings

Cu ½x10mm	013G4192
Cu ½x12mm	013G4193
Cu ½x14mm	013G4194
Cu ½x15mm	013G4195
Cu ½x16mm	013G4196



PEX and AluPEX fittings

PEX ½x12x1,1mm	013G4197
PEX ½x15x2,5mm	013G4199
PEX ½x16x2mm	013G4198
AluPEX ½x16x2mm	013G4200



Pipe set

½" nipple connection	013G3127
----------------------	----------



Heating element with stay for VHX-Duo (angle)

Stay	013G4166
150 watt chrome	013G4167
300 watt chrome	013G4168
600 watt chrome	013G4169



Wall rosettes for 50mm connections (single set)

White RAL 9016	013G3128
Chrome	013G3129
Inox	013G3131

