

Instructions

ESM-11

ENGINEERING
TOMORROW



1

2

3

4

5

6

7

8

9

10

11

12

0,3 - 1,5 mm²

Ø 3 - 7 mm

MIN:
Ø 21 mm
DN15

MAX:
Ø 76 mm
DN65

Ω

1550

1500

1450

1400

1350

1300

1250

1200

1150

1100

1050

1000

0 20 40 60 80 100 120 °C