



Relief Valves Technical Information

Direct Acting


VME 07

OPERATION


This is a direct-acting, poppet-type relief valve that relieves from 1 to 2. It features a highly damped poppet for smooth and stable response.

SPECIFICATIONS

Theoretical performance



Schematic




Specifications

Rated pressure	315 bar [4500 psi]
Rated flow	50 l/min [13 US gal/min]
Weight	0.20 kg [0.44 lb]
Cavity	VME07

DIMENSIONS

mm [in]

Cross-sectional view



ORDERING INFORMATION

VME 07 - E - 2 - DG1/2 - V - XXX			
Adjustment	E = Internal screw M = Handwheel	Seals V = Viton Omit = Buna-N	Seal kit Consult factory Consult factory
Setting range	1 = 25 - 80 bar [363-1160 psi] 2 = 35 - 180 bar [508-2611 psi] 3 = 70 - 315 bar [1015-4569 psi]	Housing and ports 00 = No Housing DG1/2 = AI, 1/2 BSP DG8S = AI, #8 SAE Other housings available	Housing P/N No Housing VME07-DG-1/2 VME07-DG-8S

To order this valve with a specific factory setting, contact your Danfoss ICS representative.