

MP Male Pipe NPTF – Rigid

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AMP6 (06-104)	10 -6	1/4-18
4S4AMP6 (06-106)	10 -6	3/8-18
4S4AMP6 (06-108)	10 -6	1/2-14
4S4AMP8 (08-112)	12 -8	3/4-14
4S4AMP8	12 -8	1/4-18
4S4AMP8	12 -8	3/8-18
4S4AMP8 (08-108)	12 -8	1/2-14
4S4AMP10 (10-112)	16 -10	3/4-14
4S4AMP10 (10-108)	16 -10	1/2-14
4S4AMP12 (12-108)	19 -12	1/2-14
4S4AMP12 (12-112)	19 -12	3/4-14
4S4AMP12 (12-116)	19 -12	1-11/12
4S4AMP16 (16-112)	25 -16	3/4-14
4S4AMP16 (16-116)	25 -16	1-11/12
4S4AMP16 (16-120)	25 -16	1 1/4-11/2
4S4AMP20 (20-116)	31 -20	1-11/12
4S4AMP20 (20-120)	31 -20	1 1/4-11/2
4S4AMP24 (24-124)	38 -24	1 1/2-1 1/2
4S4AMP32 (32-132)	51 -32	2-1 1/2
6S	DN Dash size	In
6S4AMP20 (20-120)	31 -20	1 1/4-11/2
6S4AMP24 (24-124)	38 -24	1 1/2-1 1/2
6S4AMP32 (32-132)	51 -32	2-1 1/2

MB Male O-ring Boss – Rigid

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AMB6 (06-P06)	10 -6	9/16-18
4S4AMB6 (06-P08)	10 -6	3/4-16
4S4AMB8	12 -8	7/8-14
4S4AMB8	12 -8	3/4-16
4S4AMB10 (10-P10)	16 -10	7/8-14
4S4AMB10 (10-P12)	16 -10	1 1/16-12
4S4AMB12 (12-P12)	19 -12	1 1/16-12
4S4AMB16 (16-P16)	25 -16	1 5/16-12
4S4AMB20 (20-P20)	31 -20	1 5/8-12
4S4AMB24 (24-P24)	38 -24	1 7/8-12
6S	DN Dash size	In
6S4AMB20 (20-P20)	31 -20	1 5/8-12
6S4AMB24 (24-P24)	38 -24	1 7/8-12

MJ Male JIC/37° – Rigid

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AMJ6 (06-500)	10 -6	9/16-18
4S4AMJ6 (06-508)	10 -6	3/4-16
4S4AMJ8 (08-510)	12 -8	7/8-14
4S4AMJ8	12 -8	3/4-16
4S4AMJ8 (08-508)	12 -8	1 1/16-12
4S4AMJ10 (10-510)	16 -10	7/8-14
4S4AMJ10 (10-512)	16 -10	1 1/16-12
4S4AMJ12 (12-510)	19 -12	7/8-14
4S4AMJ12 (12-512)	19 -12	1 1/16-12
4S4AMJ12 (12-514)	19 -12	1 3/16-12
4S4AMJ12 (12-516)	19 -12	1 5/16-12
4S4AMJ16 (16-516)	25 -16	1 5/16-12
4S4AMJ16 (16-520)	25 -16	1 5/8-12
4S4AMJ20 (20-520)	31 -20	1 5/8-12
4S4AMJ24 (24-524)	38 -24	1 7/8-12
4S4AMJ32 (32-532)	51 -32	2 1/2-12

FJ Female JIC/37° Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFJ6 (06-600)	10 -6	7/16-20
4S4AFJ6 (06-606)	10 -6	9/16-18
4S4AFJ6 (06-608)	10 -6	3/4-16
4S4AFJ8 (08-610)	12 -8	7/8-14
4S4AFJ8 (08-612)	12 -8	1 1/16-12
4S4AFJ8 (08-606)	12 -8	9/16-18
4S4AFJ8 (08-608)	12 -8	3/4-16
4S4AFJ10 (10-610)	16 -10	7/8-14
4S4AFJ10 (10-612)	16 -10	1 1/16-12
4S4AFJ10 (10-616)	16 -10	7/8-14
4S4AFJ12 (12-612)	19 -12	1 1/16-12
4S4AFJ12 (12-614)	19 -12	1 3/16-12
4S4AFJ12 (12-616)	19 -12	1 5/16-12
4S4AFJ16 (16-612)	25 -16	1 1/16-12
4S4AFJ16 (16-616)	25 -16	1 5/16-12
4S4AFJ16 (16-620)	25 -16	1 5/8-12
4S4AFJ20 (20-616)	31 -20	1 5/16-12
4S4AFJ20 (20-620)	31 -20	1 5/8-12
4S4AFJ24 (24-624)	38 -24	1 7/8-12
4S4AFJ32 (32-632)	51 -32	2 1/2-12
6S	DN Dash size	In
6S4AFJ20 (20-620)	31 -20	1 5/8-12
6S4AFJ24 (24-624)	38 -24	1 7/8-12
6S4AFJ32 (32-632)	51 -32	2 1/2-12

FJA Female JIC/37° Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFJA6 (06-680)	10 -6	9/16-18
4S4AFJA6 (06-688)	10 -6	3/4-16
4S4AFJA8 (08-690)	12 -8	7/8-14
4S4AFJA8 (08-698)	12 -8	3/4-16
4S4AFJA10	16 -10	7/8-14
4S4AFJA10 (10-692)	16 -10	1 1/16-12
4S4AFJA12 (12-692)	19 -12	1 1/16-12
4S4AFJA12 (12-696)	19 -12	1 5/16-12
4S4AFJA16 (16-696)	25 -16	1 5/16-12
4S4AFJA16 (16-697)	25 -16	1 5/8-12
4S4AFJA20 (20-697)	31 -20	1 5/8-12
4S4AFJA24 (24-698)	38 -24	1 7/8-12
6S	DN Dash size	In
6S4AFJA20 (20-697)	31 -20	1 5/8-12
6S4AFJA24 (24-698)	38 -24	1 7/8-12

FJB Female JIC/37° Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFJB6 (06-660)	10 -6	9/16-18
4S4AFJB6 (06-668)	10 -6	3/4-16
4S4AFJB8 (08-670)	12 -8	7/8-14
4S4AFJB8 (08-678)	12 -8	3/4-16
4S4AFJB10 (10-670)	16 -10	7/8-14
4S4AFJB10 (10-672)	16 -10	1 1/16-12
4S4AFJB12 (12-672)	19 -12	1 1/16-12
4S4AFJB12 (12-676)	19 -12	1 5/16-12
4S4AFJB16 (16-676)	25 -16	1 5/16-12
4S4AFJB16 (16-677)	25 -16	1 5/8-12
4S4AFJB20 (20-677)	31 -20	1 5/8-12
4S4AFJB24 (24-678)	38 -24	1 7/8-12
6S	DN Dash size	In
6S4AFJB20 (20-677)	31 -20	1 5/8-12
6S4AFJB24 (24-678)	38 -24	1 7/8-12

FJC Female JIC/37° Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFJC6 (06-464)	10 -6	9/16-18
4S4AFJC8 (08-468)	12 -8	7/8-14
4S4AFJC12 (12-462)	19 -12	1 1/16-12
4S4AFJC16 (16-466)	25 -16	1 5/16-12
4S4AFJC20 (20-471/50)	31 -20	1 5/8-12
6S	DN Dash size	In
6S4AFJC20 (20-471/50)	31 -20	1 5/8-12

FJG Female JIC/37° Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFJG12 (12-C62)	19 -12	1 1/16-12
4S4AFJG16 (16-C66)	25 -16	1 5/16-12
6S	DN Dash size	In
6S4AFJG20 (20-C20)	31 -20	1 1/4-11/2
6S4AFJG24 (24-C24)	38 -24	1 1/2-1 1/2
6S4AFJG32 (32-C32)	51 -32	2-1 1/2

FRA Female ORS Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFRA6 (06-566)	10 -6	1 1/16-16
4S4AFRA6 (06-568)	10 -6	1 3/16-16
4S4AFRA8 (08-570)	12 -8	1-14
4S4AFRA8	12 -8	1 1/16-16
4S4AFRA8 (08-568)	12 -8	1 3/16-16
4S4AFRA10	16 -10	1-14
4S4AFRA10 (10-570)	16 -10	1-14
4S4AFRA10 (10-572)	16 -10	1 3/16-12
4S4AFRA12 (12-570)	19 -12	1 7/16-12
4S4AFRA12 (12-572)	19 -12	1 3/16-12
4S4AFRA16 (16-572)	25 -16	1 3/16-12
4S4AFRA16 (16-576)	25 -16	1 7/16-12
4S4AFRA16 (16-580)	25 -16	1 11/16-12
4S4AFRA20 (20-580)	31 -20	1 11/16-12
4S4AFRA24 (24-584)	38 -24	2 -12
6S	DN Dash size	In
6S4AFRA20 (20-580)	31 -20	1 11/16-12
6S4AFRA24 (24-584)	38 -24	2 -12

FRB Female ORS Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFRB6 (06-A26)	10 -6	1 1/16-16
4S4AFRB6 (06-A30)	10 -6	1 1/16-16
4S4AFRB8 (08-A30)	12 -8	1 1/16-16
4S4AFRB8	12 -8	1 1/16-16
4S4AFRB8 (08-A32)	12 -8	1 3/16-12
4S4AFRB8 (08-A36)	12 -8	1 1/16-16
4S4AFRB10 (10-A30M)	16 -10	1-14
4S4AFRB10 (10-A30)	16 -10	1-14
4S4AFRB12 (12-A32)	19 -12	1 3/16-12
4S4AFRB12 (12-A36)	19 -12	1 1/16-12
4S4AFRB16 (16-A36)	25 -16	1 3/16-12
4S4AFRB16 (16-A30)	25 -16	1 7/16-12
4S4AFRB20 (20-A40)	31 -20	1 1/16-12
4S4AFRB24 (24-A44)	38 -24	2 -12
4S4AFRB24 (24-A48)	38 -24	2 -12
6S	DN Dash size	In
6S4AFRB20 (20-A40)	31 -20	1 1/16-12
6S4AFRB24 (24-A48)	38 -24	2 -12

FRC Female ORS Swivel

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S4AFRC6 (06-A66)	10 -6	1 1/16-16
4S4AFRC6 (06-A68)	10 -6	1 3/16-16
4S4AFRC8 (08-A70)	12 -8	1-14
4S4AFRC8 (08-A68)	12 -8	1 3/16-16
4S4AFRC10	16 -10	1 3/16-12
4S4AFRC10 (10-A70)	16 -10	1-14
4S4AFRC12 (12-A72)	19 -12	1 3/16-12
4S4AFRC12 (12-A76)	19 -12	1 1/16-12
4S4AFRC16 (16-A76)	25 -16	1 7/16-12
4S4AFRC16 (16-A70)	25 -16	1 1/16-12
4S4AFRC20 (20-A80)	31 -20	1 1/16-12
4S4AFRC20 (20-A84)	31 -20	2 -12
4S4AFRC24 (24-A88)	38 -24	2 -12
6S	DN Dash size	In
6S4AFRC20 (20-A80)	31 -20	1 1/16-12
6S4AFRC24 (24-A88)	38 -24	2 -12

FL SAE Code 61 Flange

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S12FL8 (08-G12)	12 -8	-
4S12FL8 (08-G08)	12 -8	-
4S12FL10 (10-G12)	16 -10	-
4S12FL12 (12-G12)	19 -12	-
4S12FL12 (12-G16)	19 -12	-
4S20FL12 (12-G20)	19 -12	-
4S16FL16 (16-G16)	25 -16	-
4S20FL16 (16-G20)	25 -16	-
4S24FL16 (16-G24)	25 -16	-
4S20FL20 (20-G20)	31 -20	-
4S20FL20 (20-G24)	31 -20	-
4S24FL20 (20-G24)	31 -20	-
4S32FL20 (20-G32)	31 -20	-
4S24FL24 (24-G24)	38 -24	-
4S32FL24 (24-G32)	38 -24	-
4S32FL32 (32-G32)	51 -32	-
6S	DN Dash size	In
6S20FL20 (20-G20)	31 -20	-
6S24FL24 (24-G24)	38 -24	-
6S32FL24 (24-G32)	38 -24	-
6S32FL32 (32-G32)	51 -32	-

FLD SAE Code 61 Flange

Part Number	Hose Size	Thread
4S	DN Dash size	In
4S12FLD8 (08-H02)	12 -8	-
4S12FLD8 (08-H01)	12 -8	-
4S12FLD12 (12-H02)	19 -12	-
4S16FLD12 (16-H03)	25 -16	-
4S16FLD16 (16-H04)	25 -16	-
4S20FLD20 (20-H04)	31 -20	-
4S20FLD20 (20-H05)	31 -20	-
4S24FLD24 (24-H05)	38 -24	-
4S32FLD24 (24-H06)	38 -24	-
4S32FLD32 (32-H06)	51 -32	-
6S	DN Dash size	In
6S20FLD20 (20-D20)	31 -20	-
6S24FLD24 (24-D24)	31 -20	-
6S24FLD24 (24-D24)	38 -24	-
6S32FLD24 (24-D32)	38 -24	-
6S32FLD32 (32-D32)	51 -32	-

FLF SAE Code 61 Flange

Part Number	Hose Size	Thread
-------------	-----------	--------