

Installation guide

Solenoid valve

Type EV310A



520B1034

520B1034

<p>A</p>	<p>B NC C NO</p>	<p><input checked="" type="checkbox"/></p> <p>>50 mesh (<297 Microns)</p> <hr/> <p><input checked="" type="checkbox"/></p> <p>ON OFF</p> <p>24h</p>
<p>1</p>	<p>2</p>	<p>3</p> <p>ID</p>
<p>4A</p>	<p>5A</p> <p>3/8" MAX 1/4" Ø</p>	<p>6A</p> <p>3/8" MAX 1/4" Ø</p>
<p>7A</p>	<p>8A</p>	<p>9A</p>

Імпортер: ТОВ з іі "Данфосс ТОВ" 04080, Київ 80, п/с 168, Україна

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

4B

5B

4C

5C

6BC

7BC

8BC

2.6 Nm ± 0.2 Nm

9B

9C

10

1.4 Nm ± 0.3 Nm

11

55 Nm ± 5 Ncm

12

13

DN	Max. Working Pressure (MWP) [bar]	Max. Test pressure (MTP) [bar]
1.2 NC	20	30
1.2 NO	13	19.5
1.5 NC / FL	12	18
1.5 NO	7	10.5
2 NC	8	12

EN 60730-2-8