



Installation guide

Solenoid valve
Type EV227B




032R9277


032R9277




≥ 50 mesh (≤ 297 Microns)




1




2




3




4



5



6



Імпортёр: ТОВ з іі "Данфосс ТОВ" 04080, Київ 80, п/с 168, Україна

Info for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB

7

8

9

10

80 - 90 Ncm
(0.59 – 0.66 lb-ft)

320 - 370 Ncm
(2.36 – 2.73 lb-ft)

11

12

DN	Max. working pressure (MWP)	Max. test pressure (MTP)
	[bar]	[bar]
10 - 22	10	15

EN 60730-2-8

Visit www.products.danfoss.com for further technical data.

Para más información, visite www.products.danfoss.es

Rendez-vous sur le site www.products.danfoss.fr pour plus de données techniques.

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.