

Instructions

Accessories – Catalogue


2	❶		R 1/8	003H6852		SW 12 (14 Nm)	SW 10
			R 3/8	003H6853		SW 12 (14 Nm)	SW 17
			R 1/2	003H6854		SW 12 (14 Nm)	SW 22
			–	003H6860		SW 12 (14 Nm)	SW 12 (14 Nm)
	❷		G 1/8	003H6931		SW 12 (14 Nm)	SW 14
				003H6932			
	❸		R 1/8	003H6857		SW 12 (14 Nm)	SW 10
			R 3/8	003H6858		SW 12 (14 Nm)	SW 17
			R 1/2	003H6859		SW 12 (14 Nm)	SW 22







4	A	B	C		A	B	C																					
			<table><tr><th>DN (mm)</th><th>EN 10226-1</th></tr><tr><td>15</td><td>G 3/4</td></tr><tr><td>20</td><td>G 1</td></tr><tr><td>25</td><td>G 1 1/4</td></tr><tr><td>32</td><td>G 1 3/4</td></tr></table>		DN (mm)	EN 10226-1	15	G 3/4	20	G 1	25	G 1 1/4	32	G 1 3/4	<table><tr><th>DN (mm)</th><th>SW (mm)</th></tr><tr><td>15</td><td>32</td></tr><tr><td>20</td><td>41</td></tr><tr><td>25</td><td>50</td></tr><tr><td>32</td><td>63</td></tr></table>		DN (mm)	SW (mm)	15	32	20	41	25	50	32	63		
					DN (mm)	EN 10226-1																						
					15	G 3/4																						
					20	G 1																						
					25	G 1 1/4																						
32	G 1 3/4																											
DN (mm)	SW (mm)																											
15	32																											
20	41																											
25	50																											
32	63																											




5			

7		

8			

1		R 1/8	003H6852		SW 12 (14 Nm)	SW 10
		R 3/8	003H6853		SW 12 (14 Nm)	SW 17
		R 1/2	003H6854		SW 12 (14 Nm)	SW 22
		–	003H6860		SW 12 (14 Nm)	SW 12 (14 Nm)
2		G 1/8	003H6931		SW 12 (14 Nm)	SW 14
			003H6932			
3		R 1/8	003H6857		SW 12 (14 Nm)	SW 10
		R 3/8	003H6858		SW 12 (14 Nm)	SW 17
		R 1/2	003H6859		SW 12 (14 Nm)	SW 22





A

B

C

DN (mm)	EN 10226-1
15	G 3/4
20	G 1
25	G 1 1/4
32	G 1 3/4

DN (mm)	SW (mm)
15	32
20	41
25	50
32	63

A
1



2

B
1

2


C
1

2




AVPBT/AVT, AVPBT/STM


1




2





3




5




4





AVPQT/AVT, AVPQT/STM




AVT/AVT/VG(F), AVT/AVT/VGS, STM/AVT/VG(F), STM/AVT/VGS







P/J033,1/01




P/J034,1/01




P/J035,1/01




P/J036,1/01




P/J037,1/01




P/M,132,1/01




P/M,133,1/01




1




2




3



4



5



6

