

# Installation guide

## Capacity regulation with pulse solenoid valves EVRP 6 and EVRP 10

032R9503

032R9503

<p><b>Max. working pressure:</b> 42 bar / 600 psig</p>	<p><b>Ambient temperature:</b> Min.: - 60 °C / -75 °F Max.: 80 °C / 175 °F</p>
<p><b>Opening differential pressure <math>\Delta p</math>:</b> MOPD (vapour): 21 bar (300 psi) MOPD (liquid): 10 bar (145 psi)</p>	<p><b>Media temperature max.:</b> 120 °C / 250 °F</p>



