

# DEVtemp™ Fan Heater



The **DEVtemp™ fan heater** is a complete portable heating system that provides a temporary but efficient heating solution. The fan heater is designed to withstand heat and cold, damp and heavy use on construction sites.

The built-in thermostat ensures that the required temperature remains constant, while keeping electricity consumption as low as possible. The fan heater can be used as a portable heater or be permanently installed.

## Benefits:

- Rugged construction
- Corrosion-resistant
- Portable or permanent installation
- Easy regulation, five-step control unit for airflow
- Thermostat to ensure required temperature remains constant
- IP Class 44

## Standard compliance:

- IEC60335-2-30



Type	Value
Timer thermostat	On types named "T" up to 24 hours presetting.
Adjustable thermostat	3 - 6 KW 0 °C to 40 °C. 9 - 21 KW 0 °C to 40 °C.
Safety thermostat	3 - 6 KW = 110 °C. 9 - 21 KW = 160 °C. 3 - 21 KW = 125 °C.
IP Class	IP 44
Colour	RAL 7004

## Types

Item no.	Type	W x H x D [mm]	Volatage	K / W	m <sup>3</sup> / h	ΔT Temp. [°C]	Weight [kg]	dB	EAN no.
69810562	303T	410 x 435 x 420	230 V~	3	400 / 650	14 / 19	12.0	32 - 35	5703464010633
69810554	103T	410 x 435 x 420	3 x 400 V~	3	400 / 650	14 / 19	13.9	32 - 35	5703464010619
69811537	106T	410 x 435 x 420	3 x 400 V~	6	400 / 650	21 / 28	14.2	33 - 42	5703464010626
69812543	109T	410 x 435 x 420	3 x 400 V~	9	400 / 650	36 / 45	14.9	33 - 42	5703464010039
69812550	115S	505 x 540 x 510	3 x 500 V~	15	800 / 1400	26 / 30	23.6	42 - 52	5703466168196
69813509	115T	505 x 540 x 510	3 x 400 V~	15	800 / 1400	26 / 30	23.6	42 - 52	5703464003437
69814515	121T	505 x 540 x 510	3 x 400 V~	21	800 / 1400	36.5 / 42	25.7	42 - 52	5703464008432

## Accessories

Item no.	Type	Specification	EAN no.
19400514	Wall mounting kit	For DEVtemp™ 303T, 103T, 106T, 109T	5703435010464
19400522	Wall mounting kit	For DEVtemp™ 115S, 115T, 121T	5703435010471