

Technical request form Vineyards

Make it easy,
make it DEVI



In order to start design the project, please provide all initial required data.

1. **Operation voltage:** _____ V
2. **Maximum allowed power for electrical heating system** _____ kW
3. **Minimum ambient temperature:** _____ °C
4. **Maintain temperature:** _____ °C
5. **Wind velocity:** _____ m/s
6. **Length of vineyard row:** _____ m
7. **Number of vineyard rows:** _____ pcs.
8. **Desired heating element:**

| | | |
|--------------------------------------|------------------------------------|------------------------------------|
| <input type="checkbox"/> Ready made: | <input type="checkbox"/> DEVIsnow™ | <input type="checkbox"/> DEVIsafe™ |
| <input type="checkbox"/> Drum Goods: | <input type="checkbox"/> DEVIsnow™ | <input type="checkbox"/> DEVIsafe™ |
9. **Control system:**
 DEVIreg™ 330 (5 - 45 °C)
 DEVIreg™ 330 (-10 - +10 °C)
 DEVIreg™ Multi
10. **Comments and Special Remarks:**

For technical questions, please, contact EH@danfoss.com