




SVL Flexline™ Parts Program

Housings

Valve Housing SVL												
DN (mm)	Size (Inch)	DIN-Butt weld		ANSI-Butt weld		GOST-Butt-weld		SOC		FPT		T
		ANG	STR	ANG	STR	ANG	STR	ANG	STR	ANG	STR	
6	¼	148B5002	148B5003	148B5004	148B5005							148B5012
10	¾	148B5122	148B5123	148B5124	148B5125	148B5134	148B5135					
15	½	148B5252	148B5253	148B5254	148B5255	148B5391	148B5392	148B5256	148B5257	148B5258	148B5259	
20	¾	148B5352	148B5353	148B5354	148B5355	148B5393	148B5394	148B5356	148B5357	148B5358	148B5359	
25	1	148B5452	148B5453	148B5454	148B5455	148B5498	148B5499	148B5456	148B5457	148B5458	148B5459	
32	1¼	148B5576	148B5577	148B5578	148B5579	148B5593	148B5594	148B5580	148B5581	148B5582	148B5583	
40	1½	148B5652	148B5653	148B5654	148B5655	148B5681	148B5682	148B5656	148B5657			
50	2	148B5741	148B5742	148B5743	148B5744	148B5759	148B5760	148B5745	148B5746			
65	2½	148B5816	148B5817	148B5818	148B5819	148B5816	148B5817					
80	3	148B5912	148B5913	148B5914	148B5915	148B5912	148B5913					
100	4	148B6014	148B6015	148B6016	148B6017	148B6033	148B6034					
125	5	148B6112	148B6113	148B6114	148B6115	148B6133	148B6134					
150	6	For valves of this size order Complete Valves										
200	8											

Service kit				
DN (mm)	Size (Inch)	O-ring kit* for		Gasket High temp. for SVA-65BT
		R717 Heat pump	R1270 Propylene	
6	¼			
10	¾	148B6084	148B6085	
15	½	148B6070	148B6077	
20	¾			
25	1			
32	1¼	148B6071**	148B6078**	
40	1½	148B6096***	148B6097***	
50	2	148B6072	148B6079	148B6808****
65	2½	148B6073	148B6080	148B6809****
80	3	148B6074	148B6081	148B6810****
100	4	148B6075	148B6082	148B6811****
125	5	148B6076	148B6083	

SVA-S & SVA-L:	
SCA-X:	
CHV-X:	
REG-S & REG-L:	
FIA:	

Inserts & Spare Parts

DN (mm)	Size (Inch)	Stop Valves				Check Valves	Check Valves	Regulating Valves				FIA Top Complete w/o Strainer	Filters								Spareparts	
		SVA-S		SVA-L		SCA-X	CHV-X	REG-SA	REG-SB	REG-LA	REG-LB		FIA: Filter insert-plain				FIA: Filter insert-pleated				Cap	Hand wheel
		Cap	Hand wheel	Cap	Hand wheel	Cap	Cap	Cap	Cap	Cap	Cap		100µ	150µ	250µ	500µ	50µ	150µ	250µ	500µ		
6	¼	148B5013	148B5014																			
10	¾							148B5112	148B5113													
15	½	148B5276	148B5277	148B5278	148B5279	148B5282	148B5283	148B5280	148B5281	148B6401	148B6402	148B5284	148H3122	148H3124	148H3126	148H3128	148H3412	148H3303	148H3363		148B4075	148B4060
20	¾																					
25	1																					
32	1¼	148B5476	148B5477	148B5478	148B5479	148B5482	148B5483	148B5480	148B5481	148B6403	148B6404	148B5484	148H3123	148H3125	148H3127	148H3129	148H3413	148H3304	148H3269		148B4076	148B4062
40	1½																					
50	2	148B5728	148B5729			148B5735	148B5747		148B5734			148B5748	148H3157	148H3130	148H3138	148H3144	148H3414	148H3179	148H3184	148H3189		148B4064
65	2½	148B5822	148B5823			148B5825	148B5827		148B5824			148B5832		148H3131	148H3139	148H3145	148H3415	148H3180	148H3185	148H3190		
80	3	148B5916	148B5917			148B5918	148B5919					148B5922		148H3119	148H3120	148H3121	148H3416	148H3181	148H3186	148H3191	148B4077	148B4065
100	4	148B6012	148B6018			148B6019	148B6022					148B6024		148H3132	148H3140	148H3146	148H3417	148H3182	148H3187	148H3192		148B4066
125	5	148B6116	148B6117			148B6118	148B6119					148B6122		148H3133	148H3141	148H3147	148H3418	148H3183	148H3188	148H3193	148B4078	148B4067

* to be used for SCA-X, CHV-X and REG SA/SB (all sizes)

** to be used for SCA-X, CHV-X, 25-40

*** to be used for REG SA/SB, 25-40

**** Max. temperature 190 °C (374 °F)

Danfoss A/S
Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

AF477920057001en-000301

© Danfoss | Climate Solutions | 2025.04

See how tomorrow's solutions are ready today
visit www.danfoss.com/IR

ENGINEERING
TOMORROW

Danfoss