

■ PERFORMANCE DATA

Duty cycle	100% at 110% rated voltage between -20°C and 40°C
Magnet wire insulation	200°C [392° F]
Input Voltage Range	90% to 110% of rated voltage

■ MODEL CODE

C13 - H - 24 - 22

Coil Series
C13 -13 mm tube

Connector Type

Code	Connector Type
H	DIN43650 ISO Standard
F	Flying Leads [12 and 24 VDC only]
DM	Deutsch Moulded [12 and 24 VDC only]

Coil Power
14 -14 Watt
22 -22 Watt
27 -27 Watt

Coil Voltage

Code	Coil Voltage
12	12 VDC
24	24 VDC
110	110 VAC*
220	220 VAC*

*External rectifier required:AXP9997-115 or AXP9997-230

■ DIMENSIONS

mm [in]

