

■ PERFORMANCE DATA

Duty cycle	100% at 110% of rated voltage
Magnet wire insulation	U.L. class N, 200°C [392°F] NEMA pub. No. MW 1000, section MW 35 – C [single]
Ambient temperature	100°C [212°F] continuous @ rated voltage
Input Voltage Range	85% to 110% of rated voltage

■ ENVIRONMENT PROTECTION

Rating	Connector Type
IP69K	NO
Thermal shock dunk	NO

■ ELECTRICAL SPECIFICATIONS

Voltage	12 VDC	24 VDC
Current (A)	0.78	0.41
Power (W)	10	10

*Nominal voltage 25°C (77°F).

■ MODEL CODE

MCSC - K - 012 - D - NO - 0 - 00 - 10

Coil Series
K - Size 10 [210 Bar]

Coil Voltage

Code	Coil Voltage
012	12 volt
024	24 volt

Voltage Type
D - DC

Lead Length
0 - None

Connector Type
NO - Deutsch

■ PART NUMBERS

Voltage	NO Connector
12VDC	12007809
24VDC	12007810

■ DIMENSIONS

mm [in]

NO
Deutsch male DT04-2P integrated connector

