

■ PERFORMANCE DATA

Duty cycle	100% at 110% rated voltage between -20°C and 40°C
Magnet wire insulation	200°C [392° F]
Input Voltage Range	90% to 110% of rated voltage

■ MODEL CODE

C16 - H - 24 - 19

Coil Series
C16 -16 mm tube

Connector Type

Code	Connector Type
H	DIN43650 ISO Standard
F	Flying Leads [12 and 24 VDC only]
DM	Deutsch Moulded [12 and 24 VDC only]

Coil Power
19 -19 Watt
29 -29 Watt

Coil Voltage

Code	Coil Voltage
12	12 VDC
24	24 VDC
110	110 VAC*
220	220 VAC*

*External rectifier required:AXP9997-115 or AXP9997-230

■ DIMENSIONS

mm [in]

