

■ ENVIRONMENT PROTECTION

Rating	Connector Type
IP65	All other connectors
IP69K	DE

■ ELECTRICAL SPECIFICATIONS

Voltage	12 VDC	24 VDC
Resistance (Ohms) @ 20 °C [68 °F]	4.7 Ω	19.0 Ω
Power (W)	30W	30W

■ MODEL CODE

MCSC - 024 - D - C - E - 06

Coil Voltage

Code	Coil Voltage
012	12 VDC
024	24 VDC

Voltage Type

D - DC

Lead length

00 - None
05 - 127mm [5.0 in]
06 - 152mm [6.0 in]

Series

E - E series, 30W

Connector Type

Code	Connector Type
G	ISO 4400 DIN 43650
W	Flying lead
C	Deutsch Male, DT04-2P, On wire leads

*DIN 43560 mating connector for "G" style coil: 02-166796"

■ COIL KITS

Model code	Part number
MCSC-012-D-G-E-00	6034440-001
MCSC-024-D-G-E-00	6034440-002
MCSC-012-D-W-E-00	6034441-001
MCSC-012-D-C-E-06	6034442-002

■ DIMENSIONS

mm [in]

