

# High efficiency and reliability

Optimized refrigeration in a compact design



**-40 °F to +50 °F**  
extended  
compressor range

Danfoss MLZ scroll compressors for medium temperature applications are dedicated to commercial and light commercial refrigeration applications.

Thanks to their unique scroll design, MLZ scroll compressors deliver a number of powerful advantages, such as reduced energy costs, high-capacity cooling, and an optimized pressure ratio.


See how tomorrow's solutions are ready today.  
Visit [choose.danfoss.com](http://choose.danfoss.com)

ENGINEERING  
TOMORROW

*Danfoss*

# Technical data and ordering

## MLZ - Medium Temperature Scroll Compressors



Model No.	HP	Nominal capacity (Btu/h)*				Connection Type	Individual packaged	Individual Packaged	
		R-404A	R-449A	R-134a	R-513A			Rotolock (in.)	Weight (LBS.)
MLZ015	2.0	15,400	14,600	9,600	9,900	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	68	121U8709	121U8711
MLZ019	2.5	21,000	19,300	12,800	12,900	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	68	121U8719	121U8723
MLZ021	3.0	22,500	20,500	13,600	13,700	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	68	121U8737	121U8739
MLZ026	3.5	27,800	25,500	16,800	17,100	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	68	121U8751	121U8753
MLZ030	4.0	32,600	31,100	20,300	20,800	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	90	121U8763	121U8765
MLZ038	5.0	39,300	35,700	23,900	24,700	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	90	121U8775	121U8777
MLZ045	6.0	47,600	44,200	28,400	29,900	1 in.-14UN(2A) x 1 1/4 in.-12UN(2A)	90		121U8797
MLZ048	7.0	51,800	48,500	30,400	32,600	1 in.-12UN(2A) x 1 1/4 in.-12UN(2A)	90		121U8807
MLZ058	7.5	57,900	57,300	36,700	38,000	1 1/4 in.-12UN(2A) x 1 3/4 in.-12UN(2A)	104		121U8817
MLZ076	10.0	78,800	70,300	47,300	47,400	1 1/4 in.-12UN(2A) x 1 3/4 in.-12UN(2A)	104		121U8835

\*Nominal capacity @ ASHRAE MT

For the performance data of other refrigerants or conditions, use Coolselector<sup>®</sup>2 (<http://bit.ly/CoolSelector2>) or ODSG (<http://bit.ly/DanfossODSG>). MLZ line is qualified for the following refrigerants: R-404A, R-507, R-134a, R-407A, R-407F, R-448A, R-449A, R-452A and R-513A.

### Solder sleeve adapter sets



Code n°	Description	Application	Packaging	Pack size
120Z0126	Rotolock adaptor set (1-1/4" ~ 3/4"), (1" ~ 1/2")	MLZ015-019-021-026	Multipack	6
120Z0127	Rotolock adaptor set (1-1/4" ~ 7/8"), (1" ~ 1/2")	MLZ030-038-042-045	Multipack	6
120Z0128	Rotolock adaptor set (1-1/4" ~ 7/8"), (1-1/4" ~ 3/4")	MLZ048	Multipack	6
120Z0129	Rotolock adaptor set (1-3/4" ~ 1-1/8"), (1-1/4" ~ 7/8")	MLZ058-066-076	Multipack	6

### Rotolock nuts and sleeves kit



Code n°	Description	Application	Packaging	Pack size
120Z5074	Rotolock nuts 1 1/4 and 1" with sleeves and gaskets	MLZ015-045	Multipack	6
120Z5076	2 Rotolock nuts 1 1/4 with sleeves and gaskets	MLZ048	Multipack	6
120Z5075	Rotolock nuts 1 1/4 and 1 3/4 with sleeves and gaskets	MLZ058-066-076	Multipack	6

MLZ compressors are also available with braze connections. For further information, contact Danfoss at 1-888-DANFOSS

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.