







12 11 10 9 8 7 6 5 4 3 2 1

H  
G  
F  
E  
D  
C  
B  
A




Type	Value
IP Class	-
UL Type	-
Enclosure Colour	grey
Frame Size	AAF01




Dimension [mm]	Tolerances				
	<250	250>x>800	>800	parts in series	folded parts
Tolerance [mm]	+/-1	+/-2.5	+/-4	+/-2.5	+/-2.5

ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale		
			1:4		
Gezeichnet	2022-10-13	FR	AAF 007 Airduct (2+6) AAF01		
Kontrolliert					
Name			136b3273		
Status	Änderungen	DATUM	Name	REV	001
				Sheet 1 of 3	Size A1

12 11 10 9 8 7 6 5 4 3 2 1



Cabinet mounting plate



ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		Projection	Scale	
			2:1	
Gezeichnet	DATUM	Name		
Kontrolliert	2022-10-13	FR		
Name			AAF 007 Airduct (2+6) AAF01	
			136b3273	REV 001
Status	Änderungen	DATUM	Name	Size A1
				Sheet 2 of 3