




Standard




Standard with Decoupling kits



Mounting-Base



Standard with Nema-Option



Standard with IP21-Option

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.  
CENTER OF GRAVITY:  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

| UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS: ± 0.4 INCH   |                 | FIRST ANGLE PROJECTION |       | SCALE  | DRAWING SIZE | MATERIAL |                 |
|---|-----------------|------------------------|-------|--------|--------------|----------|-----------------|
| ALL DIMENSIONS ARE IN MILLIMETERS [INCH]  |                 |                        |       | 1:2    | A1           |          | -               |
| FINISH  |                 |                        |       |        |              |          | -               |
| DESCRIPTION   |                 |                        |       |        |              |          |                 |
| CHANGED   |                 |                        |       |        |              |          | IC2-Micro-MA01a |
| DESIGNED  | DANFOSS         | 05/30/22               |       |        |              |          |                 |
| CHECKED   |                 |                        |       |        |              |          |                 |
| DRAWING NUMBER  | IC2-Micro-MA01a |                        | REV   | P1     |              |          |                 |
| MODEL   |                 |                        | SHEET | 1 OF 1 |              |          |                 |
| PROPERTY OF DANFOSS A/S NØRDBØRG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S. |                 |                        |       |        |              |          |                 |