



additional informations:
 filter colour : RAL5008 / R9006
 filter weight : 142kg

label:

VLT MCC 101 sine wave FILTER www.denfoss.com		SINCE 45 SØNDERSBOG, DENMARK	
E 210222 100000000		MOUNTING BRACKET Cx=354H P=654 T=1100 100000000	
E 210222 100000000		SINCE 45 SØNDERSBOG, DENMARK	
E 210222 100000000		SINCE 45 SØNDERSBOG, DENMARK	

f108.05.16| Schr./Fie. | type/label updated. Denfoss Postadress included

e10.11.14	Schr./Fie.	type/label updated
d102.04.13	Heu./Schr.	type/label updated
c102.04.13	Schr./Kor.	type/label updated
b11.03.13	Schr./Kor.	type/label updated
a01.10.10	KOR/Lauer	approval added
date	name	amendment

Dimensions toleranced according to ISO 2768-m

Tolerance class	from 0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	01.06.10	Kornau	Kornau	scale	1:12,5
checked	01.06.10	Bremer	Bremer	format	A4
date		name	signature	DIN ISO 5456	

order number	130B4117	drawing number	Z791004036	modi.	f	sheet	1/1
Please observe protection clause to ISO 16016							

Dimensions B 1002052.2

Sine-wave filter 690V 76A – IP23

