



Name	
Date	



Distribution	
IN →	10
	6
	5
← OUT	3

1. Tube: 16X1.3X16ports;
2. FPI=23;
3. Inlet and outlet tubes are copper;
4. Range of the operating temperature of refrigerant side: -40°C to 121°C (-40°F to 250°F);
5. The design pressure of MCHE is 4.5MPa(652.7Psia);
6. Internal hold-up volume: 0.15L;
7. 021U0341 is for industrial pack
021U0510 is for multi pack

MRK	REVISION RECORD				DRN	DATE	Linear Tolerance Not Specified				Projection	Scale	Size	Angle Tolerance Not Specified	
A2	Add a size	LS.CHEN	2024.02.01			≤6	>6-30	>30-120	>120-400		2 : 3	A2	0°/90°/180°	Other Angle	
						±0.5	±1	±1.5	±2.5				±2°	±3°	
						>400-1000 >1000-2000 >2000-4000							Designation		
						±4	±6	±8					Condenser		
						DRN H.Jin									
						APP									
						DATE 2016.06.13			Customer PN:						
						Confidential: Property of Danfoss A/S, Nordborg, Denmark. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss A/S.						NO. X0-DM0010		REV. 06	
												WT. 0.640 kg			