




REVISION RECORD				DRN	APP	DATE
MRK	△ Add a size			LS.CHEN		2024.02.01

Technical requirement:
1.Tube:16X1.3X16ports;
2FPI=23;
3.Inlet and outlet tubes are copper;
4.Range of the operating temperature of refrigerant side: -40°C to 121°C (-40°F to 250°F);
5.The design pressure of MCHE is 4.5MPa(652.7Psia);
6.Internal hold-up volume:0.19L.

Distribution	
IN	10
	6
	5
OUT	3

Linear Tolerance Not Specified					Scale 1 : 2	Size A3	Angle Tolerance Not Specified	
≤6	>6-30	>30-120	>120-400				0°/90°/180°	Other Angle
±0.5	±1	±1.5	±2.5				±2°	±3°
>400-1000	>1000-2000	>2000-4000				Designation		
±4	±6	±8				Condenser		
DRN	H.Jin							
APP								
DATE	2016.06.13							
Confidential: Property of Danfoss A/S, Nordborg, Denmark. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss A/S.						Customer P/N:		
						NO. X0-DM0020		REV. 06
						WT. 1.000 kg		