








Technical requirements:

- 1.Connector tolerance not specified refers to ISO 2768-1-M
- 2.Other linear tolerance not specified:±2

Design Pressure(PS)	3.0MPa(30bar)
Testing Pressure(N ₂)	4.5MPa(45bar)
Design Temperature(TS)	-196/+200℃
Leak Testing	He
Volume(L)	12.81L/Q1Q2Side;12.6L/Q3Q4Side
Weight(kg)	55.66Kg
Danfoss Code	021B6358
Label Code	F-MP-107



Bolt verticality :±2°
Connection verticality :±2°
Plate material: 316L
Connection: 304L
Cover plate: 304L

Standardization	2024.01.12	Projection	Scale	Size	Material	Danfoss Standard: 500B0598
	2009.12.23		2:1	A4		
Mrk	ECR/Comments	Date				
DRN						Designation
CHK						B3-095-122-3.0-HQ-
MFG						Q1Q2(L2B)/Q3(H1"1/8)
APP						/Q4(H2"1/8)/
						Installation Drawing
Confidential:Property of Danfoss A/S Nordborg, Denmark.Not to be handed over to copied or used by third party.Two-or three dimensional reproduction of contents to be authorized by Danfoss A/S.						T1432-027
						2009.10.25
						B/2

